

Cat5e Patch Cable with Molded RJ45 Connectors - 10 ft. - Gray

Produkt ID: M45PATCH10GR



The M45PAT10GR Cat5e Patch Cable (10 ft) meets or exceeds all Cat 5e specifications to ensure reliable Ethernet network connections, and features a durable gray PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat5e patch cable features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Cat5e Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat5e cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat 5e cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This molded patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Certifikat, rapporter och kompatibilitet



Användning

- Framtagen för att användas med snabba Ethernet-nätverk
- Kopplar från hubb till distributionspanel
- Anslut en arbetsstation till ett vägguttag

Funktioner

- Gjutna RJ45-kontakter
- Tillverkad och testad med omsorg för att bakåtöverhörning (NEXT) ska ligga väl inom godkända gränser
- Färgade huvor så att man kan färgkoda olika avdelningar
- Tillverkad av komponenter med toppkvalitet
- Högkvalitativ 0,25 mm² koppartråd

Hårdvara

Garantipolicy	Lifetime
Antal ledare	4 Pair UTP
Kabelmanteltyp	PVC - Polyvinyl Chloride
Brandteknisk klass	CMG-klass (General Purpose)
Kabeltyp	Gjuten
Kabelstandard	TIA/EIA-568-B.1-2001 T568B

Prestanda

Kabelklassificering	CAT5e - 350 MHz
---------------------	-----------------

Kontakt(er)

Connector A	1 - RJ-45
-------------	-----------

Connector B	1 - RJ-45
Miljö	
Drifttemperatur	-20 (-4°F) - 60 (140°F)
Förvaringstemperatur	0 (32°F) - 30 (86°F)
Luftfuktighet	60%RH
Utseende	
Färg	Grå
Tråddimension	24 AWG
Ledningstyp	Tvinnad koppar
Kabellängd	10.0 ft [3.0 m]
Produktlängd	10.0 ft [3.0 m]
Produktbredd	0.5 in [1.2 cm]
Produkthöjd	0.6 in [1.4 cm]
Produktvikt	3.6 oz [102.0 g]
Förpackning	
Förpackningsantal	1
Paketets längd	6.5 in [16.4 cm]
Paketets bredd	7.8 in [19.8 cm]
Paketets höjd	1.0 in [2.5 cm]
Fraktvikt (förpackning)	3.6 oz [102.0 g]
Vad det är i lådan	
Ingår i paketet	1 - 10 ft. Cat5e Patch Cable - Gray
Warranty Information	
Warranty	Livslängd

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.