

15 ft Cat5e Black Molded RJ45 UTP Cat 5e Patch Cable - 15ft Patch Cord

Produkt ID: M45PATCH15BK



The M45PAT15BK Cat5e Patch Cable (15 ft) meets or exceeds all Cat 5e specifications to ensure reliable Ethernet network connections, and features a durable black PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat5e patch cable features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Cat5e Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat5e cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat 5e cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This molded patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Certifikat, rapporter och kompatibilitet



Användning

- Framtagen för att användas med snabba Ethernet-nätverk
- Kopplar från hubb till distributionspanel
- Anslut en arbetsstation till ett vägguttag
- Förläng dina Ethernet-nätverksenheters räckvidd med 4,5 m

Funktioner

- Gjutna RJ45-kontakter
- Tillverkad och testad med omsorg för att bakåtoverhörning (NEXT) ska ligga väl inom godkända gränser
- Färgade huvor så att man kan färgkoda olika avdelningar
- Tillverkad av komponenter med toppkvalitet
- Högkvalitativ 0,25 mm² koppartråd

Hårdvara

Garantipolicy	Lifetime
Antal ledare	4 Pair UTP
Kabelmanteltyp	PVC - Polyvinyl Chloride
Brandteknisk klass	CMG-klass (General Purpose)
Kabeltyp	Gjuten
Kabelstandard	TIA/EIA-568-B.1-2001 T568B

Prestanda

Kabelklassificering	CAT5e - 350 MHz
---------------------	-----------------

Kontakt(er)

Connector A	1 - RJ-45
Connector B	1 - RJ-45

Miljö

Drifttemperatur	-20 (-4°F) - 60 (140°F)
Förvaringstemperatur	0 (32°F) - 30 (86°F)
Luftfuktighet	60%RH

Utseende

Färg	Svart
Tråddimension	24 AWG
Ledningstyp	Tvinnad koppar
Kabellängd	15.0 ft [4.6 m]
Produktlängd	15.0 ft [4.6 m]
Produktbredd	0.5 in [1.2 cm]
Produkthöjd	0.5 in [1.2 cm]
Produktvikt	5.3 oz [150.0 g]

Förpackning

Förpackningsantal	1
Paketets längd	8.7 in [22.0 cm]
Paketets bredd	7.9 in [20.0 cm]
Paketets höjd	0.8 in [2.0 cm]
Fraktvikt (förpackning)	5.6 oz [160.0 g]

Vad det är i lådan

Ingår i paketet	1 - 15 Ft Black Molded Cat5 Patch Cable
-----------------	---

Warranty Information

Warranty	Livslängd
----------	-----------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.