

1 ft Cat5e Red Molded RJ45 UTP Cat 5e Patch Cable - 1ft Patch Cord

Produkt ID: M45PATCH1RD



The M45PAT10RD Cat5e Patch Cable (1 ft) meets or exceeds all Cat 5e specifications to ensure reliable Ethernet network connections, and features a durable red PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat5e patch cable features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.


Constructed of only top quality materials, this Cat5e Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat5e cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat 5e cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This molded patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Certifikat, rapporter och kompatibilitet



Användning

- Designed for use with Fast Ethernet networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet

Funktioner

- Molded RJ45 connectors
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- Colored hoods for departmental color coding
- Constructed with top quality components
- High quality 24 AWG copper wire

Hårdvara

Garantipolicy	Lifetime
Antal ledare	4 pair UTP
Kabelmanteltyp	PVC - Polyvinyl Chloride
Brandteknisk klass	CMG-klass (General Purpose)
Kabeltyp	Gjuten
Kabelstandard	TIA/EIA-568-B.1-2001 T568B

Prestanda


Kabelklassificering	CAT5e - 350 MHz
---------------------	-----------------

Kontakt(er)

Connector A	RJ-45
Connector B	RJ-45

Utseende

Färg	Röd
Tråddimension	24 AWG



Kabellängd 12.0 in [30.5 cm]

Produktlängd 12.0 in [30.5 cm]

Förpackning

Package Length 7.8 in [19.9 cm]

Package Width 0.4 in [10 mm]

Package Height 8.3 in [21.1 cm]

Fraktvikt (förpackning) 1.1 oz [30 g]

Vad det är i lådan

Ingår i paketet 1 Ft Red Molded Cat 5 Patch Cable

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

