

Cat5e Patch Cable with Molded RJ45 Connectors - 20 ft. - Gray

Productcode: M45PATCH20GR



The M45PAT20GR Cat5e Patch Cable (20 ft) meets or exceeds all Cat 5e specifications to ensure reliable Ethernet network connections, and features a durable gray PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat5e patch cable features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Cat5e Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat5e cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat 5e cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This molded patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Certificaties, rapporten en compatibiliteit



Toepassingen

- Designed for use with Fast Ethernet networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet
- Extend the reach of your Ethernet network devices by 20 ft

Eigenschappen

- Molded RJ45 connectors
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- Colored hoods for departmental color coding
- Constructed with top quality components
- High quality 24 AWG copper wire

Hardware

Garantiebeleid	Lifetime
Aantal geleiders	4 Pair UTP
Type kabelmantel	PVC - Polyvinyl Chloride
Brandbestendigheid	CMG goedgekeurd (algemeen doel)
Type kabel	Gegoten

Connector(en)

Connector A	1 - RJ-45
Connector B	1 - RJ-45

Gebruiksomgeving

Bedrijfstemperatuur	-20 (-4°F) - 60 (140°F)
---------------------	-------------------------

	Opslagtemperatuur	0 (32°F) - 30 (86°F)
	Vochtigheid	60%RH
Fysieke eigenschappen		
	Kleur	Grijs
	Draaddikte	24 AWG
	Type geleider	Gevlochten koper
	Kabellengte	20.0 ft [6.1 m]
	Lengte product	20.0 ft [6.1 m]
	Breedte product	0.5 in [1.2 cm]
	Hoogte product	0.5 in [1.4 cm]
	Gewicht product	7.9 oz [224.0 g]
Verpakkingsinformatie		
	Verpakkingsaantal	1
	Lengte Verpakking	8.0 in [20.4 cm]
	Package Width	8.7 in [22.0 cm]
	Package Height	1.6 in [4.0 cm]
	Verzendgewicht (verpakt)	8.6 oz [244.0 g]
Wat wordt er meegeleverd		
	Meegeleverd	1 - 20 ft. Cat5e Patch Cable - Gray
Garantiebepalingen		
	Warranty	Levenslang

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.