

Cat5e Patch Cable with Molded RJ45 Connectors - 30 ft. - Blue

Produkt-ID: M45PATCH30BL



The M45PATCH30BL Cat5e Patch Cable (30 ft) meets or exceeds all Cat 5e specifications to ensure reliable Ethernet network connections, and features a durable blue PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat5e patch cable features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Cat5e Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat5e cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat 5e cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This molded patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Designed for use with Fast Ethernet networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet
- Extend the reach of your Ethernet network devices by 30 ft

Merkmale

- Molded RJ45 connectors
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- Colored hoods for departmental color coding
- Constructed with top quality components
- High quality 24 AWG copper wire

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	4 pair UTP
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Feuerwiderstandssklasse	Ausgelegt gemäß CMG (Mehrzweck)
Kabeltyp	Vergossen
Verkabelungsstandard	TIA/EIA-568-B.1-2001 T568B

Leistung

Kabelnennwerte	CAT5e - 100 MHz
----------------	-----------------

Steckverbinder

Steckverbinder A	1 - RJ-45
Steckverbinder B	1 - RJ-45

Umgebungsbedingungen

Betriebstemperatur	-20 (-4°F) - 60 (140°F)
Lagertemperatur	0 (32°F) - 30 (86°F)
Feuchtigkeit	60%RH

Physische Eigenschaften

Farbe	Blau
Drahtstärke	24 AWG
Leitungstyp	Feindrähtiges Kupfer
Kabellänge	30.0 ft [9.1 m]
Produktlänge	30.0 ft [9.1 m]
Produktbreite	0.4 in [1.1 cm]
Produkthöhe	0.4 in [1.0 cm]
Produktgewicht	10.0 oz [282.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	13.0 in [33.0 cm]
Paketbreite	10.0 in [25.5 cm]
Pakethöhe	0.8 in [2.1 cm]
Versandgewicht (Verpackung)	10.5 oz [298.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 30 ft. Cat5e Patch Cable - Blue
--------------------	-------------------------------------

Garantieinformatio
nen

Warranty

Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.