

Cat5e Patch Cable with Molded RJ45 Connectors - 3 ft. - Black

ID prodotto: M45PATCH3BK



The M45PAT3BK Cat5e Patch Cable (3 ft) meets or exceeds all Cat 5e specifications to ensure reliable Ethernet network connections, and features a durable black PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat5e patch cable features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Cat5e Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat5e cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat 5e cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This molded patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Certificazioni, report e compatibilità



Applicazioni

- Designed for use with Fast Ethernet networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet

Caratteristiche

- Molded RJ45 connectors
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- Colored hoods for departmental color coding
- Constructed with top quality components
- High quality 24 AWG copper wire

Hardware

Norme di garanzia	Lifetime
Numero di conduttori	4 Pair UTP
Tipo guaina cavo	PVC - Polyvinyl Chloride
Classe di resistenza al fuoco	Classe CMG (uso generale)
Tipo cavo	Modellato
Standard cablaggio	TIA/EIA-568-B.1-2001 T568B

Prestazioni

Classe cavo	CAT5e - 100 MHz
-------------	-----------------

Connettore/i

Connettore A	1 - RJ-45
--------------	-----------

Connettore B		1 - RJ-45
Ambientale		
	Temperatura d'esercizio	-20 (-4°F) - 60 (140°F)
	Temperatura di conservazione	0 (32°F) - 30 (86°F)
	Umidità	60%RH
Caratteristiche fisiche		
	Colore	Nero
	Diametro filo	24 AWG
	Tipo di conduttore	Rame intrecciato
	Lunghezza del cavo	3.0 ft [0.9 m]
	Lunghezza prodotto	3.0 ft [0.9 m]
	Larghezza prodotto	0.5 in [1.2 cm]
	Altezza prodotto	0.3 in [8.0 mm]
	Peso prodotto	1.3 oz [36.0 g]
Informazioni confezione		
	Quantità confezione	1
	Lunghezza Confezione	7.7 in [19.5 cm]
	Larghezza del Pacco	7.7 in [19.6 cm]
	Altezza del Pacco	0.8 in [2.1 cm]
	Peso spedizione (confezione)	1.7 oz [48.0 g]
Contenuto della confezione		
	Incluso nella confezione	1 - 3 ft. Cat5e Patch Cable - Black

Informazioni sulla
garanzia

Warranty

A vita

* L'aspetto e le specifiche dell'articolo sono soggetti a modifiche senza preavviso.