

Cat5e Patch Cable with Molded RJ45 Connectors - 3 ft. - Blue

ID del Producto: M45PATCH3BL



The M45PAT3BL Cat5e Patch Cable (3 ft) meets or exceeds all Cat 5e specifications to ensure reliable Ethernet network connections, and features a durable blue PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat5e patch cable features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Cat5e Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat5e cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat 5e cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This molded patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Certificaciones, Reportes y Compatibilidad



Aplicaciones

- Diseñada para su uso en redes Fast Ethernet
- Conecta un hub a un panel de distribución
- Conecta una estación de trabajo a una placa de pared

Características

- Conectores RJ45 moldeados
- Cuidadosamente fabricado y probado, para mantener los niveles de diafonía (Near End Crosstalk) en límites aceptables
- Cubiertas de colores para ayudar a codificarlo por color de sección o departamento
- Fabricado con componentes de la más alta calidad
- Alambre de cobre alta calidad con 24AWG

Hardware

Política de Garantía	Lifetime
Cantidad de Conductores	4 Pair UTP
Cable Tipo Jacket	PVC - Polyvinyl Chloride
Grado de Inflamabilidad	Clasificación CMG (uso general)
Tipo de Cable	Moldeado
Estándar de Cableado	TIA/EIA-568-B.1-2001 T568B

Rendimiento

Clasificación de Cables	CAT5e - 100 MHz
-------------------------	-----------------

Conector(es)

Conector A	1 - RJ-45
Conector B	1 - RJ-45

Requisitos Ambientales

Temperatura Operativa	-20 (-4°F) - 60 (140°F)
Temperatura de Almacenamiento	0 (32°F) - 30 (86°F)
Humedad	60%RH

Características Físicas

Color	Azul
Calibre del Conductor	24 AWG
Tipo de conductor	Cobre trenzado
Longitud del Cable	3.0 ft [0.9 m]
Longitud del Producto	3.0 ft [0.9 m]
Ancho del Producto	0.5 in [1.2 cm]
Altura del Producto	0.4 in [1.0 cm]
Peso del Producto	1.3 oz [36.0 g]

Información de la Caja

Cantidad de Paquetes	1
Longitud de la Caja	8.1 in [20.5 cm]
Ancho de la Caja	7.8 in [19.8 cm]
Altura de la Caja	0.6 in [1.4 cm]
Peso (de la Caja) del Envío	1.7 oz [48.0 g]

Contenido de la Caja

Incluido en la Caja	1 - Cable de red Cat5e de 91cm - Azul
---------------------	---------------------------------------

Información Acerca
de la Garantía

Warranty

De Por Vida

* La apariencia y las especificaciones del producto están sujetas a cambios sin previo aviso.