Cat5e Patch Cable with Molded RJ45 Connectors - 3 ft. - Green

Product ID: M45PATCH3GN

The M45PAT3GN Cat5e Patch Cable (3 ft) meets or exceeds all Cat 5e specifications to ensure reliable Ethernet network connections, and features a durable green PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat5e patch cable features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Cat5e Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat5e cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat 5e cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This molded patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Certifications, Reports and Compatibility

Applications

• Designed for use with Fast Ethernet networks

• Patches from hub to distribution panel

• Connects workstation to wall outlet

Features

• Molded RJ45 connectors

• Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits

• Colored hoods for departmental color coding

• Constructed with top quality components

• High quality 24 AWG copper wire

Hardware		
	Warranty	Lifetime
	Number of Conductors	4 pair UTP
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Fire Rating	CMG Rated (General Purpose)
	Cable Type	Molded
	Wiring Standard	TIA/EIA-568-B.1-2001 T568B
Performance		
	Cable Rating	CAT5e - 350 MHz
Connector(s)		
	Connector A	1 - RJ-45
	Connector B	1 - RJ-45
Physical Characteristics		
	Color	Green
	Wire Gauge	24 AWG

	Conductor Type	Stranded Copper
	Cable Length	3.0 ft [0.9 m]
	Product Length	3.0 ft [0.9 m]
	Weight of Product	1.3 oz [36 g]
Packaging Information		
	Package Quantity	1
	Package Length	8.7 in [22 cm]
	Package Width	7.9 in [20 cm]
	Package Height	0.4 in [10 mm]
	Shipping (Package) Weight	1.6 oz [45 g]
What's in the Box		
	Included in Package	1 - 3 ft. Cat5e Patch Cable - Green

Product appearance and specifications are subject to change without notice.