

Cable reseau Cat5e moule de 91 cm - Gris

N° de produit: M45PATCH3GR



The M45PAT10GR Cat5e Patch Cable (3 ft) meets or exceeds all Cat 5e specifications to ensure reliable Ethernet network connections, and features a durable gray PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat5e patch cable features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Cat5e Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat5e cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat 5e cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This molded patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Certifications, rapports et compatibilité



Applications

- Designed for use with Fast Ethernet networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet

Spécifications techniques

- Molded RJ45 connectors
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- Colored hoods for departmental color coding
- Constructed with top quality components
- High quality 24 AWG copper wire

Matériel

Politique de garantie	Lifetime
Nombre de conducteurs	4 Pair UTP
Type de gaine de câble	PVC - Polyvinyl Chloride
Résistance au feu	Homologué CMG (usage général)
Type de câble	Moulé
Norme de câblage	TIA/EIA-568-B.1-2001 T568B

Performance

Calibre du câble	CAT5e - 100 MHz
------------------	-----------------

Connecteur(s)

Connecteur A	1 - RJ-45
--------------	-----------

Connecteur B 1 - RJ-45

Conditions environnementales

Température de fonctionnement	-20 (-4°F) - 60 (140°F)
Température de stockage	0 (32°F) - 30 (86°F)
Humidité	60%RH

Caractéristiques physiques

Couleur	Gris
Calibre du fil	24 AWG
Type de conducteur	Cuivre torsadé
Longueur de câble	3.0 ft [0.9 m]
Longueur du produit	3.0 ft [0.9 m]
Largeur du produit	0.5 in [1.2 cm]
Hauteur du produit	0.4 in [1.1 cm]
Poids du produit	1.3 oz [37.0 g]

Informations d'emballage

Quantité par paquet	1
Longueur du Paquet	7.6 in [19.3 cm]
Largeur du Colis	5.9 in [15.1 cm]
Hauteur du Paquet	0.7 in [1.9 cm]
Poids brut	1.6 oz [44.0 g]

Contenu du paquet

Inclus dans le paquet	1 - 3 ft. Cat5e Patch Cable - Gray
-----------------------	------------------------------------

Informations de garantie

Warranty

À Vie

* L'apparence et les spécifications du produit peuvent être modifiées sans préavis