Cat5e Patch Cable with Molded RJ45 Connectors - 75 ft. - Blue

Nº de produit: M45PATCH75BL

The M45PAT75BL Cat5e Patch Cable (75 ft) meets or exceeds all Cat 5e specifications to ensure reliable Ethernet network connections, and features a durable blue PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat5e patch cable features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Cat5e Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat5e cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat 5e cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This molded patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Certifications, rapports et compatibilité

Applications

- Designed for use with Fast Ethernet networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet
- Extend the reach of your Ethernet network devices by 75 ft

Spécifications techniques

- Molded RJ45 connectors
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- Colored hoods for departmental color coding
- Constructed with top quality components
- High quality 24 AWG copper wire

Matériel		
	Politique de garantie	Lifetime
	Nombre de conducteurs	4 pair UTP
	Type de gaine de câble	PVC - Polyvinyl Chloride
	Résistance au feu	Homologué CMG (usage général)
	Type de câble	Moulé
	Norme de câblage	TIA/EIA-568-B.1-2001 T568B
Performance		
	Calibre du câble	CAT5e - 100 MHz
Connecteur(s)		

	Connecteur A	1 - RJ-45
	Connecteur B	1 - RJ-45
Conditions environnementales		
	Température de fonctionnement	-20 (-4ºF) - 60 (140ºF)
	Température de stockage	0 (32ºF) - 30 (86ºF)
	Humidité	60%RH
Caractéristiques physiques		
	Couleur	Bleu
	Calibre du fil	24 AWG
	Type de conducteur	Cuivre torsadé
	Longueur de câble	75.0 ft [22.9 m]
	Longueur du produit	75.0 ft [22.9 m]
	Poids du produit	26.1 oz [740 g]
Informations d'emballage		
	Quantité par paquet	1
	Longueur du Paquet	10.2 in [26.0 cm]
	Largeur du Colis	0.9 in [2.2 cm]
	Hauteur du Paquet	9.4 in [23.9 cm]
	Poids brut	1.8 lb [0.8 kg]
Contenu du paquet		
	Inclus dans le paquet	1 - 75 ft. Cat5e Patch Cable - Blue
Informations de garantie		
	Warranty	À Vie

* L’apparence et les spécifications du produit peuvent être modifiées sans préavis