

10 ft DB25 to DB9 Serial Modem Cable - M/F

Product ID: MC10MF



StarTech.com AT modem cables are fully molded and shielded for reliability and durability in any environment - capable of supporting sustained transfer rates in excess of 430 kbps with an extremely low error rate, making them suitable for any application.

Certifications, Reports and Compatibility

Applications

- Connects 9 pin serial port to modem
- Connects 9 pin serial port to a switchbox

Features

Connector(s)

| | |
|-------------|-----------------------|
| Warranty | Lifetime |
| Connector A | DB-9 (9 pin, D-Sub) |
| Connector B | DB-25 (25 pin, D-Sub) |

Physical Characteristics

| | |
|-------|------|
| Color | Gray |
|-------|------|

| | |
|--------------|-----------------|
| Cable Length | 10.0 ft [3.0 m] |
|--------------|-----------------|

| | |
|----------------|-----------------|
| Product Length | 10.0 ft [3.0 m] |
|----------------|-----------------|

Packaging Information

| | |
|----------------|------------------|
| Package Length | 4.8 in [12.2 cm] |
|----------------|------------------|

| | |
|---------------|----------------|
| Package Width | 0.6 in [16 mm] |
|---------------|----------------|

| | |
|----------------|------------------|
| Package Height | 8.5 in [21.6 cm] |
|----------------|------------------|

| | |
|---------------------------|----------------|
| Shipping (Package) Weight | 6.0 oz [170 g] |
|---------------------------|----------------|

What's in the Box

| | |
|---------------------|---------------------|
| Included in Package | 10 FOOT MODEM CABLE |
|---------------------|---------------------|

****Product appearance and specifications are subject to change without notice.***

