

3ft (1m) Mini DisplayPort Cable, 8K 60Hz HDR10, Ultra HD 4K 120Hz Video, mDP 1.4
Cable for Monitors Displays, Mini DisplayPort Cord - M/M

Produkt-ID: MDISPLPORT3



This Mini DisplayPort™ 1.4 cable features 2 Mini DP male connectors, and offers a dependable solution for connecting any Mini DisplayPort-enabled laptop (including Mac® family of products) to a Mini DisplayPort-equipped monitor.

The mDP cable supports high resolutions of up to 8k (7680 x 4320) @ 60Hz with a maximum HBR3 bandwidth of 32.4 Gbps. The cable also supports Multi-Stream (MST) for daisy chaining multiple monitors and provides optional audio support.

Ensures reliable performance and proper display of digitally protected content, with support for both HDCP and DPCP.

Newer laptop and desktop computers (e.g. Apple®) come equipped with Thunderbolt™ ports only. Our Mini DisplayPort Cables can be connected to the Thunderbolt ports, enabling you to connect your Mini DP compatible displays.

Please note: This is not a Thunderbolt cable, and therefore does not work for Thunderbolt peripherals (displays, docks, drive enclosures, audio interfaces, etc).

Zertifikate Berichte und Kompatibilität



Anwendungen

- Schließen Sie Mini DisplayPort-Laptop oder -Desktop an ein Mini DisplayPort-kompatibles Display an

Merkmale

- **COMPATIBILITY NOTE:** This is not a Thunderbolt cable and is not compatible with Thunderbolt peripherals such as Docking Stations, Displays or External Enclosures; It can however be used to connect a Thunderbolt 2 laptop to a Mini-DisplayPort monitor
- **HIGH PERFORMANCE:** Mini DisplayPort 1.4 cable; 8K 60Hz (7680x4320p), 4K 120Hz (3840x2160p), 32.4Gbps bandwidth, HDR10, 32Ch Audio, MST, GTC for precise audio channel timing; future-proof your equipment by making it 8K ready
- **RELIABLE DESIGN:** Durable ABS connectors with flexible PVC strain relief and jacket prevents fraying or damage due to bending or rough usage; Metal connector sub-structure provides EMI shielding
- **HOCHWERTIGE KONSTRUKTION:** 32AWG Draht mit vergoldeten Steckern zur Verbesserung der Signalintegrität und zuverlässigkeit; überlegene EMI Abschirmung mit doppelseitiger Kupferfolie für höhere Video/Audioqualität; mDP Kabel ist rückwärtskompatibel mit DP1.1
- **SPEZIFIKATIONEN:** 91cm; Schwarzes Mini DP Kabel; DisplayPort v1.2; mDP Stecker auf mDP Stecker Kabel; 32 AWG; PVC Kabel Mantel, ABS Stecker Gehäuse; Abschirmung: Al-Mylar Folie mit Geflecht; Protokolle: HBR2, MST, GTC; Unterstützt auf Lebenszeit

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	19
Steckverbinderplatten	Nickel
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Feuerwiderstandssklasse	Ausgelegt gemäß CMG (Mehrzweck)e

Leistung

Max. Digitalauflösungen	4k x 2k (3840 x 2160) @ 60Hz
-------------------------	------------------------------

Steckverbinder

Steckverbinder A	1 - Mini-DisplayPort (20-polig)
Steckverbinder B	1 - Mini-DisplayPort (20-polig)

Umgebungsbedingungen

Betriebstemperatur	-20°C to 50°C (-4°F to 122°F)
Lagertemperatur	-20°C to 60°C (-4°F to 140°F)
Feuchtigkeit	0~75% RH

Physische Eigenschaften

Farbe	Schwarz
Drahtstärke	32 AWG
Kabellänge	3.0 ft [0.9 m]
Außendurchmesser des Kabels	0.2 in [4.8 mm]
Produktlänge	36.0 in [91.4 cm]
Produktbreite	0.4 in [1.1 cm]
Produkthöhe	0.3 in [8.4 mm]
Produktgewicht	1.2 oz [35.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	7.2 in [18.4 cm]
Paketbreite	7.8 in [19.8 cm]
Pakethöhe	0.6 in [1.6 cm]
Versandgewicht (Verpackung)	1.6 oz [44.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 91cm Mini-DisplayPort-Kabel - M/M
--------------------	---------------------------------------

Garantieinformationen

Warranty

Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.