

10 ft Mini DisplayPort to DisplayPort 1.2 Adapter Cable M/M - DisplayPort 4k

Product ID: MDP2DPMM10



The MDP2DPMM10 10ft Mini DisplayPort to DisplayPort Adapter Cable, features a Mini DP male connector on one end, and a DP male connector on the other, allowing you to connect any Mini DisplayPort-equipped laptop (including the Mac family of products) to an HDTV, monitor or projector that uses a standard DisplayPort connection.

The mDP to DP cable supports high resolutions of up to 4k x 2k (3840 x 2160) @ 60Hz with a maximum HBR2 bandwidth of 21.6 Gbps. The cable also supports Multi-Stream (MST) for daisy chaining multiple monitors and provides optional audio support.

The MDP2DPMM10 is backed by StarTech.com's Lifetime Warranty, for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

: Newer laptop and desktop computers (e.g. Apple) come equipped with Thunderbolt ports only. Our Mini DP to DP Cables can be connected to the Thunderbolt ports, enabling you to connect your DP compatible displays.

Certifications, Reports and Compatibility



Applications

- Connect a DisplayPort monitor or projector to devices equipped with a Mini DisplayPort connection port

Features

- Gold-plated connectors
- High-resolution support of up to 4k x 2k
- Support for High Bit Rate 2 (HBR2) bandwidth of up to 21.6 Gbps

- Designed and manufactured to DisplayPort 1.2 standards
- Backward compatible with DisplayPort 1.1
- Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP

Hardware	Warranty	Lifetime
	Number of Conductors	19
	Connector Plating	Gold
	Cable Jacket Material	PVC - Polyvinyl Chloride
	Cable Shield Material	Aluminum-Mylar Foil with Braid
	Fire Rating	CMG Rated (General Purpose)
Performance	Maximum Digital Resolutions	4k x 2k (3840 x 2160) @ 60Hz
Connector(s)	Connector A	Mini-DisplayPort (20 pin)
	Connector B	DisplayPort (20 pin)
Environmental	Operating Temperature	0C to 45C (32F to 113F)
	Storage Temperature	-10C to 70C (14F to 158F)
	Humidity	10%-85% RH
Physical Characteristics	Color	Black
	Wire Gauge	32 AWG
	Cable Length	10.0 ft [3.0 m]
	Cable OD	0.2 in [4.8 mm]
	Product Length	10.0 ft [3.0 m]
	Product Width	0.0 in [0.000 mm]
	Product Height	0.0 in [0.000 mm]
	Weight of Product	3.7 oz [103.944 g]
Packaging Information	Package Length	8.7 in [2.2 cm]
	Package Width	7.9 in [2.0 cm]
	Package Height	0.9 in [22.000 mm]
	Shipping (Package) Weight	4.0 oz [112.944 g]
What's in the	Included in Package	10 ft Mini DisplayPort to DisplayPort 1.2 Adapter Cable - M/M

Box

**Product appearance and specifications are subject to change without notice.*

