

3ft (1m) Mini DisplayPort to DisplayPort 1.2 Cable - 4K x 2K UHD Mini DisplayPort to DisplayPort Adapter Cable - Mini DP to DP Cable for Monitor - mDP to DP Converter Cord

Produkt ID: MDP2DPMM1MW



The MDP2DPMM1MW 1m White Mini DisplayPort™ to DisplayPort Adapter Cable, features a Mini DP male connector on one end, and a DP male connector on the other, allowing you to connect any Mini DisplayPort-equipped laptop (including the Mac® family of products) to an HDTV, monitor or projector that uses a standard DisplayPort connection.

The mDP to DP cable supports high resolutions of up to 4k x 2k (3840 x 2160) @ 60Hz with a maximum HBR2 bandwidth of 21.6 Gbps. The cable also supports Multi-Stream (MST) for daisy chaining multiple monitors and provides optional audio support.

The MDP2DPMM1MW is backed by StarTech.com's Lifetime Warranty, for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

Please Note: Newer laptop and desktop computers (e.g. Apple®) come equipped with Thunderbolt™ ports only. Our Mini DP to DP Cables can be connected to the Thunderbolt ports, enabling you to connect your DP compatible displays.

Certifikat, rapporter och kompatibilitet



Användning

- Connect a DisplayPort monitor or projector to devices equipped with a Mini DisplayPort connection port

Funktioner

- **MINI-DP to DISPLAYPORT 1.2 CABLE:** This 1m (3.3ft) DisplayPort v1.2 cable supports 4K x 2K (3840x2160 60Hz), 21.6 Gbps bandwidth, HBR2, 8Ch Audio, Multi-Stream Transport (MST), GTC for precise audio channel timing & 3D Stereo (2560x1600p 120Hz)
- **PÅLITLIG DESIGN:** Slitstarka ABS-kontakter med flexibel PVC-dragavlastning och -mantel förhindrar slitage/skador på grund av böjning eller grov användning. Metallkontaktens understruktur ger EMI-skärmning
- **QUALITY CONSTRUCTION:** 32AWG wire with gold-plated connectors for improved signal integrity and reliability; Superior EMI shielding with Al-Mylar foil and copper braid provides higher quality video and audio; Backwards compatible with DP 1.1
- **APPLICATIONS:** Ideal for home/office/boardroom/classroom works w/laptop (with Mini-DP port)/professional workstations with AMD FirePro™ W9100/8100, Nvidia NVS 810/510 graphic card; UHD/4K monitor/projector/display; Microsoft Surface Pro 6/4
- **SPECIFIKATIONER:** 1 m. Vit. DisplayPort v1.2. Mini-DP-hane till Standard DP-hane. 32 AWG. PVC-mantel, ABS-kontakthölje. Skärmning: Al-Mylarfolie med flätning, protokoll: HBR 2, MST, GTC, stöds under hela sin livslängd

Hårdvara

Garantipolicy	Lifetime
Antal ledare	19
Kontaktplätering	Guld
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Aluminiummylarfolie med jord-tråd
Brandteknisk klass	CMG-klass (General Purpose)

Prestanda

Maximal digital upplösning	4k x 2k (3840 x 2160) @ 60Hz
----------------------------	------------------------------

Kontakt(er)

Connector A	1 - Mini-DisplayPort (20-stifts)
Connector B	1 - DisplayPort (20-stifts)

Utseende		
	Färg	Vit
	Kontakttyp	Rak
	Tråddimension	32 AWG
	Kabellängd	3.3 ft [1 m]
	Produktlängd	39.4 in [100.0 cm]
	Produktbredd	0.8 in [2.0 cm]
	Produkthöjd	1.4 in [3.7 cm]
	Produktvikt	1.4 oz [40.0 g]
Förpackning		
	Förpackningsantal	1
	Paketets längd	7.3 in [18.6 cm]
	Paketets bredd	8.0 in [20.2 cm]
	Paketets höjd	0.7 in [1.8 cm]
	Fraktvikt (förpackning)	1.8 oz [52.0 g]
Vad det är i lådan		
	Ingår i paketet	1 - 1 m White Mini DisplayPort to DisplayPort 1.2 Adapter Cable - M/M
Warranty Information		
	Warranty	Livslängd

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.