

## 6ft (2m) Mini DisplayPort to DisplayPort 1.2 Cable - 4K x 2K UHD Mini DisplayPort to DisplayPort Adapter Cable - Mini DP to DP Cable for Monitor - mDP to DP Converter Cord

Produkt ID: MDP2DPMM2MW



The MDP2DPMM2MW 2m White Mini DisplayPort™ to DisplayPort Adapter Cable, features a Mini DP male connector on one end, and a DP male connector on the other, allowing you to connect any Mini DisplayPort-equipped laptop (including the Mac® family of products) to an HDTV, monitor or projector that uses a standard DisplayPort connection.

The mDP to DP cable supports high resolutions of up to 4k x 2k (3840 x 2160) @ 60Hz with a maximum HBR2 bandwidth of 21.6 Gbps. The cable also supports Multi-Stream (MST) for daisy chaining multiple monitors and provides optional audio support.

The MDP2DPMM2MW is backed by StarTech.com's Lifetime Warranty, for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

Please Note: Newer laptop and desktop computers (e.g. Apple®) come equipped with Thunderbolt™ ports only. Our Mini DP to DP Cables can be connected to the Thunderbolt ports, enabling you to connect your DP compatible displays.

### Certifikat, rapporter och kompatibilitet



### Användning

- Connect a DisplayPort monitor or projector to devices equipped with a Mini DisplayPort connection port

## Funktioner

- **MINI-DP to DISPLAYPORT 1.2 CABLE:** This 2m (6.6ft) DisplayPort v1.2 cable supports 4K x 2K (3840x2160 60Hz), 21.6 Gbps bandwidth, HBR2, 8Ch Audio, Multi-Stream Transport (MST), GTC for precise audio channel timing & 3D Stereo (2560x1600p 120Hz)
- **RELIABLE DESIGN:** Durable ABS connectors with flexible PVC strain relief & jacket prevents fraying/damage due to bending or rough usage; Metal connector sub-structure provides EMI shielding
- **QUALITY CONSTRUCTION:** 32AWG wire with gold-plated connectors for improved signal integrity and reliability; Superior EMI shielding with Al-Mylar foil and copper braid provides higher quality video and audio; Backwards compatible with DP 1.1
- **APPLICATIONS:** Ideal for home/office/boardroom/classroom works w/laptop (with Mini-DP port)/professional workstations with AMD FirePro™ W9100/8100, Nvidia NVS 810/510 graphic card; UHD/4K monitor/projector/display; Microsoft Surface Pro 6/4
- **SPECIFIKATIONER:** 2 m. Vit. DisplayPort v1.2. Mini-DP-hane till Standard DP-hane. 32 AWG; PVC-mantel, ABS-kontakthölje. Skärmning: Al-Mylarfolie med flätning, protokoll: HBR 2, MST, GTC, stöds under hela sin livslängd

---

### Hårdvara

|                    |                                   |
|--------------------|-----------------------------------|
| Garantipolicy      | Lifetime                          |
| Antal ledare       | 19                                |
| Kontaktplätering   | Guld                              |
| Kabelmanteltyp     | PVC - Polyvinyl Chloride          |
| Kabelskärmning     | Aluminiummylarfolie med jord-tråd |
| Brandteknisk klass | CMG-klass (General Purpose)       |

---

### Prestanda

|                            |                              |
|----------------------------|------------------------------|
| Maximal digital upplösning | 4k x 2k (3840 x 2160) @ 60Hz |
|----------------------------|------------------------------|

---

### Kontakt(er)

|             |                                  |
|-------------|----------------------------------|
| Connector A | 1 - Mini-DisplayPort (20-stifts) |
| Connector B | 1 - DisplayPort (20-stifts)      |

---

## Utseende

|               |                 |
|---------------|-----------------|
| Färg          | Vit             |
| Kontakttyp    | Rak             |
| Tråddimension | 32 AWG          |
| Kabellängd    | 6.6 ft [2 m]    |
| Produktlängd  | 6.6 ft [2.0 m]  |
| Produktbredd  | 0.8 in [2.0 cm] |
| Produkthöjd   | 1.4 in [3.7 cm] |
| Produktvikt   | 2.6 oz [73.0 g] |

## Förpackning

|                         |                  |
|-------------------------|------------------|
| Förpackningsantal       | 1                |
| Paketets längd          | 6.3 in [16.0 cm] |
| Paketets bredd          | 7.8 in [19.7 cm] |
| Paketets höjd           | 0.9 in [2.3 cm]  |
| Fraktvikt (förpackning) | 2.8 oz [80.0 g]  |

## Vad det är i lådan

|                 |                                                                       |
|-----------------|-----------------------------------------------------------------------|
| Ingår i paketet | 1 - 2 m White Mini DisplayPort to DisplayPort 1.2 Adapter Cable - M/M |
|-----------------|-----------------------------------------------------------------------|

## Warranty Information

|          |           |
|----------|-----------|
| Warranty | Livslängd |
|----------|-----------|

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.