

3 ft Mini DisplayPort to DVI Adapter Converter Cable – Mini DP to DVI 1920x1200 - White

Product ID: MDP2DVIMM3W



The MDP2DVIMM3W Mini DisplayPort to DVI Adapter Cable lets you directly connect your Mini DP video source (such as any of your MacBook or Microsoft Surface Pro devices with mDP) to a DVI monitor, projector, eliminating the expense of having to upgrade to a Mini DisplayPort-capable monitor.

The adapter cable is 3 feet (1 m) in length, and features male-to-male connectors, allowing you to connect your Mini DisplayPort source directly to a DVI display with no additional cabling required.

Compatible with Intel Thunderbolt, when connected directly to a supporting DisplayPort over Thunderbolt I/O port, the adapter supports resolutions up to 1920x1200 (WUXGA).

MDP2DVIMM3W is a passive adapter that requires a dual-mode DisplayPort port (DisplayPort++), meaning that DVI and HDMI signals can also be passed through the port.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Ideal for using your DVI monitor as a secondary display
- Connect your existing DVI display device (monitor, projector) to a Mini DisplayPort output device

Features

- Supports resolutions up to 1920x1200 (WUXGA) and HDTV resolutions up to 1080p

- Compatible with Intel Thunderbolt devices that are capable of outputting a DisplayPort signal
- 1x Male Mini DisplayPort connector, 1x Male DVI connector

Hardware

Warranty	3 Years
Active or Passive Adapter	Passive
AV Input	Mini DisplayPort - 1.2
AV Output	DVI-D - Single-Link
Audio	No
Chipset ID	NXP - 3361

Performance

Maximum Cable Length	36.0 in [91.5 cm]
Maximum Digital Resolutions	1920x1200 / 1080p
Wide Screen Supported	Yes
Audio Specifications	DVI - No Audio Support
MTBF	2,405,577 hours

Connector(s)

Connector A	Mini-DisplayPort (20 pin)
Connector B	DVI-D (25 pin)

Special Notes / Requirements

System and Cable Requirements	DP++ (DisplayPort++) port required from video card or video source for DVI and HDMI signal pass-through
-------------------------------	---

Environmental

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	0C to 70C (32F to 158F)
Humidity	40%-85%RH

Physical



Characteristics

Color	White
Cable Length	36.0 in [91.5 cm]
Product Length	36.0 in [91.4 cm]
Product Width	1.6 in [40 mm]
Product Height	0.6 in [15 mm]
Weight of Product	2.5 oz [71.2 g]

Packaging Information

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.8 in [20 mm]
Shipping (Package) Weight	3.0 oz [86 g]

What's in the Box

Included in Package	Mini DisplayPort to DVI Adapter
---------------------	---------------------------------

**Product appearance and specifications are subject to change without notice.*

