

6 ft Mini DisplayPort to DVI Adapter Converter Cable – Mini DP to DVI 1920x1200 - White

Product ID: MDP2DVIMM6W



The MDP2DVIMM6W Mini DisplayPort to DVI Adapter Cable lets you directly connect your Mini DP video source (such as any of your MacBook or Microsoft Surface Pro devices with mDP) to a DVI monitor or projector, eliminating the expense of having to upgrade to a Mini DisplayPort-capable monitor.

The adapter cable is 6 feet (1.8 m) in length, and features male-to-male connectors, allowing you to connect your Mini DisplayPort source directly to a DVI display with no additional cabling required.

Compatible with Intel Thunderbolt, when connected directly to a supporting DisplayPort over Thunderbolt I/O port, the adapter supports display or projector resolutions up to 1920x1200 (WUXGA).

MDP2DVIMM6W is a passive adapter that requires a dual-mode DisplayPort port (DisplayPort++), meaning that DVI and HDMI signals can also be passed through the port.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Ideal for using your DVI monitor as a secondary display
- Connect your existing DVI display device (monitor, projector) to a Mini DisplayPort output device

Features

- Supports resolutions up to 1920x1200 (WUXGA) and HDTV resolutions up to 1080p

- Compatible with Intel Thunderbolt devices that are capable of outputting a DisplayPort signal
- 1x Male Mini DisplayPort connector, 1x Male DVI connector

Hardware	Warranty	3 Years
	Active or Passive Adapter	Passive
	AV Input	Mini DisplayPort - 1.2
	AV Output	DVI-D - Single-Link
	Audio	No
	Chipset ID	NXP - 3361
Performance	Maximum Cable Length	6.0 ft [1.8 m]
	Maximum Digital Resolutions	1920x1200 / 1080p
	Wide Screen Supported	Yes
	Audio Specifications	DVI - No Audio Support
	MTBF	2,405,577 hours
Connector(s)	Connector A	Mini-DisplayPort (20 pin)
	Connector B	DVI-D (25 pin)
Special Notes / Requirements	System and Cable Requirements	DP++ (DisplayPort++) port required from video card or video source for DVI and HDMI signal pass-through
Environmental	Operating Temperature	0C to 60C (32F to 140F)
	Storage Temperature	-10C to 70C (14F to 158F)
	Humidity	40%-85%RH
Physical Characteristics	Color	White
	Cable Length	6.0 ft [1.8 m]
	Product Length	6.0 ft [1.8 m]
	Product Width	1.6 in [40 mm]
	Product Height	0.6 in [15 mm]
	Weight of Product	3.5 oz [100 g]
Packaging Information	Package Length	9.4 in [2.4 cm]
	Package Width	6.3 in [1.6 cm]

Package Height	0.8 in [20 mm]
Shipping (Package) Weight	4.4 oz [125 g]

What's in the Box	Included in Package	Mini DisplayPort to DVI Adapter
--------------------------	---------------------	---------------------------------

****Product appearance and specifications are subject to change without notice.***

