

Mini DisplayPort to VGA Adapter Cable with Audio - 10 ft (3m)

Product ID: MDP2VGAAMM3M



Now you can organize your workspace with less mess than ever before.

This unique 10-foot Mini DisplayPort to VGA adapter cable features a built-in audio port, which enables you to connect a VGA monitor as well as speakers to your Mini DisplayPort equipped desktop computer or laptop (such as any of the Microsoft Surface Pro devices) that support mDP.

Remove the cable clutter from your desk. With the built-in audio port you no longer need to run a separate audio cable from your monitor or speakers directly to your desktop or laptop computer. Simply plug the audio cable from your speakers into the adapter cable for a simple and tidy solution.

In order to use the audio function of the adapter, it needs to be powered through USB. Simply connect a Micro-USB cable into the adapter from your computer, monitor or USB grommet in order to provide the necessary power.

The adapter guarantees you always have all of the connections you need. If the audio port on your computer is damaged or blocked, this adapter cable ensures you still have sound available for watching video presentations, listening to music while you work or chatting with your colleagues over Skype.

The adapter cable is compatible with Intel Thunderbolt, when connected directly to a supporting DisplayPort over Thunderbolt I/O port, and supports resolutions up to 1920x1200 (WUXGA).

The MDP2VGAAMM3M is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Connect your speakers and a VGA monitor to your Mini DisplayPort equipped computer with the cables hidden and out of the way

- Use in your boardroom or office workstations for installations requiring 10 feet of cable

Features

- Create a clutter-free work environment by placing your audio and video cables neatly behind your monitor
- Substitute a damaged or blocked audio port by connecting your speakers to your computer directly through the adapter
- Provide crystal-clear picture quality with support for high-definition video resolutions up to 1920x1200 or 1080p

Hardware

Warranty	3 Years
Active or Passive Adapter	Active
AV Input	Mini DisplayPort - 1.2
AV Output	VGA
Audio	Yes

Performance

Maximum Analog Resolutions	1920x1200 / 1080p (output)
Maximum Digital Resolutions	1920x1200 / 1080p (input)
Wide Screen Supported	Yes
Audio Specifications	VGA - No Audio Support

Connector(s)

Connector Type(s)	USB Micro-B (5 pin)
Connector A	Mini-DisplayPort (20 pin)
Connector B	VGA (15 pin, High Density D-Sub) 3.5 mm Mini-Jack (3 Position)

Power

Power Source	USB-Powered
--------------	-------------

Environmental



Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-10C to 55C (14F to 131F)
Humidity	40%~50%RH

Physical Characteristics

Color	Black
Cable Length	9.8 ft [3 m]
Product Length	9.8 ft [3 m]
Product Width	1.6 in [39.7 mm]
Product Height	0.6 in [16.5 mm]
Weight of Product	5.2 oz [146 g]

Packaging Information

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	1.6 in [41 mm]
Shipping (Package) Weight	5.9 oz [168 g]

What's in the Box

Included in Package	3m Mini DisplayPort to VGA adapter cable with audio
	0.5m Micro USB cable

****Product appearance and specifications are subject to change without notice.***

