

10 ft Mini DisplayPort to VGA Adapter Converter Cable – mDP to VGA 1920x1200 - White

Product ID: MDP2VGAMM10W



Den MDP2VGAMM10W aktiva Mini DisplayPort till VGA-konverteringskabeln p 3m gr det mjligt att ansluta din Mini DisplayPort-utrustade enhet (Mac, Ultrabook eller annan mDP-kapabla Microsoft Surface Pro) direkt till en VGA-skrm eller -projektor utan extra adaptrar eller kablar - en kostnadseffektiv lsning fr att f din Mini DisplayPort-dator att fungera med en VGA-skrm eller-projektor. Kabeln har en elegant vit design som passar perfekt fr anslutning av Mac-datorer.

Kabeladaptorn r kompatibel med Intel Thunderbolt vid anslutning direkt till en kompatibel DisplayPort ver Thunderbolt I/O-port. Eftersom konverterarkabeln stder videoupplsningar p upp till 1920x1200 kan du dessutom konvertera en DisplayPort-videoklla till VGA utan att frlora videokvalitet.

MDP2VGAMM10W tcks av StarTech.coms 3-rsgaranti och gratis livstidsgaranti p teknisk support.

Certifications, Reports and Compatibility



Applications

- Use your VGA monitor as a secondary display, connected to a Mini DisplayPort output
- Connect a Mini DisplayPort computer to a VGA projector for presentations or meetings in a boardroom or auditorium setting
- Connect your existing VGA display device (monitor, projector) to a DisplayPort output device (PC, laptop, Mac, Ultrabook)

Features

- Active Mini DisplayPort to VGA conversion

- Plug-and-Play Installation
- Supports resolutions up to 1920x1200 (WUXGA) and HDTV resolutions up to 1080p
- Compatible with Intel Thunderbolt devices that are capable of outputting a DisplayPort signal

Hrdvara	Warranty	3 Years
	Active or Passive Adapter	Active
	AV-ingng	Mini DisplayPort - 1.2
	AV-utgng	VGA
	Audio	No
	Chipset-ID	Analogix - 9832
Prestanda	Maximal kabellngd	10.0 ft [3.0 m]
	Maximal analog uppslning	1920x1200 / 1080p (Output) 1920x1200 / 1080p (Input)
	Maximal digital uppslning	VGA - No Audio Support
	Audio-specifikationer	
Kontakt(er)	Connector A	Mini-DisplayPort (20 pin)
	Connector B	VGA (15 pin, High Density D-Sub)
Milj	Drifttemperatur	0C to 60C (32F to 140F)
	Frvaringstemperatur	-10C to 70C (14F to 158F)
	Luftfuktighet	40%-85%RH
Utseende	Frg	White
	Kabellngd	10.0 ft [3.0 m]
	Produktlngd	36.0 in [9.2 cm]
	Produktbredd	1.3 in [34 mm]
	Produktljd	0.6 in [15 mm]
	Produktvikt	5.4 oz [153 g]
Frpackning	Package Length	8.7 in [2.2 cm]
	Package Width	7.9 in [2 cm]
	Package Height	0.9 in [23 mm]
	Fraktvikt (frpackning)	5.3 oz [150 g]

Vad det r i Idan Ingr i paketet

Mini DisplayPort to VGA Adapter Cable

****Product appearance and specifications are subject to change without notice.***

