

## 10 ft Mini DisplayPort to VGA Adapter Converter Cable – mDP to VGA 1920x1200 - White

**Product ID:** MDP2VGAMM10W



The MDP2VGAMM10W 10ft active Mini DisplayPort to VGA converter cable lets you connect your Mini DisplayPort-equipped device (Mac, Ultrabook or any mDP enabled Microsoft Surface Pro) directly to a VGA monitor or projector with no additional adapters or cables required -- a cost-effective solution for enabling your Mini DisplayPort computer to work with a VGA monitor or projector. The cable features a stylish white design, that is well-suited for connecting Mac computers.

The adapter cable is compatible with Intel Thunderbolt, when connected directly to a supporting DisplayPort over Thunderbolt I/O port. Plus, because the converter cable supports video resolutions up to 1920x1200 you can convert a DisplayPort video source to VGA without sacrificing video quality.

The MDP2VGAMM10W is backed by a 3-year StarTech.com warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Use your VGA monitor as a secondary display, connected to a Mini DisplayPort output
- Connect a Mini DisplayPort computer to a VGA projector for presentations or meetings in a boardroom or auditorium setting
- Connect your existing VGA display device (monitor, projector) to a DisplayPort output device (PC, laptop, Mac, Ultrabook)

## Features

- Active Mini DisplayPort to VGA conversion
- Plug-and-Play Installation
- Supports resolutions up to 1920x1200 (WUXGA) and HDTV resolutions up to 1080p
- Compatible with Intel Thunderbolt devices that are capable of outputting a DisplayPort signal

---

### Hardware

Warranty	3 Years
Active or Passive Adapter	Active
AV Input	Mini DisplayPort - 1.2
AV Output	VGA
Audio	No
Chipset ID	Analogix - 9832

---

### Performance

Maximum Cable Length	10.0 ft [3.0 m]
Maximum Analog Resolutions	1920x1200 / 1080p (Output)
Maximum Digital Resolutions	1920x1200 / 1080p (Input)
Audio Specifications	VGA - No Audio Support

---

### Connector(s)

Connector A	1 - Mini-DisplayPort (20 pin)
Connector B	1 - VGA (15 pin, High Density D-Sub)

---

### Environmental

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	40%-85%RH

---

### Physical

### Characteristics

Color	White
Cable Length	10.0 ft [3.0 m]
Product Length	36.0 in [91.5 cm]
Product Width	1.3 in [34 mm]
Product Height	0.6 in [1.5 cm]
Weight of Product	5.4 oz [153 g]

---

### Packaging Information

Package Quantity	1
Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.9 in [23 mm]
Shipping (Package) Weight	0.3 lb [0.2 kg]

---

### What's in the Box

Included in Package	1 - Mini DisplayPort to VGA Adapter Cable
---------------------	---

---

***\*Product appearance and specifications are subject to change without notice.***