

15 ft Mini DisplayPort to VGA Adapter Converter Cable – mDP to VGA 1920x1200 - Black

**Product ID:** MDP2VGAMM15B



The MDP2VGAMM15B active Mini DisplayPort to VGA converter cable lets you connect your Mini DisplayPort-equipped desktop or laptop directly to a VGA monitor or projector at a longer distance than a standard-length cable would support, while saving the expense of additional adapters. The Mini DisplayPort adapter is the perfect accessory for any of your Microsoft Surface Pro devices with mDP.

The adapter cable is compatible with Intel Thunderbolt, when connected directly to a supporting DisplayPort over Thunderbolt I/O port. Plus, because the converter cable supports video resolutions up to 1920x1200 you can convert a DisplayPort video source to VGA without sacrificing video quality.

The MDP2VGAMM15B is backed by a 3-year StarTech.com warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Use your VGA monitor as a secondary display, connected to a Mini DisplayPort output
- Connect a Mini DisplayPort computer to a VGA projector for presentations or meetings in a boardroom or auditorium setting
- Connect your existing VGA display device (monitor, projector) to a DisplayPort output device (PC, laptop, Mac, Ultrabook)

## Features

- Active Mini DisplayPort to VGA conversion
- Plug-and-Play Installation
- Supports resolutions up to 1920x1200 (WUXGA) and HDTV resolutions up to 1080p
- Compatible with Intel Thunderbolt devices that are capable of outputting a DisplayPort signal

---

### Hardware

Warranty	3 Years
Active or Passive Adapter	Active
AV Input	Mini DisplayPort - 1.4
AV Output	VGA
Audio	No
Chipset ID	Analogix - 9832

---

### Performance

Maximum Cable Length	15.0 ft [4.6 m]
Maximum Analog Resolutions	1920x1200 / 1080p (Output)
Maximum Digital Resolutions	1920x1200 / 1080p (Input)
Audio Specifications	VGA - No Audio Support
MTBF	1,449,804 hours

---

### Connector(s)

Connector A	1 - Mini-DisplayPort (20 pin)
Connector B	1 - VGA (15 pin, High Density D-Sub)

---

### Environmental

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	40%-85%RH

---

**Physical Characteristics**

Color	Black
Cable Length	15.0 ft [4.6 m]
Product Length	15.0 ft [4.6 m]
Product Width	1.6 in [4.0 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	3.1 oz [88.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	9.4 in [24.0 cm]
Package Width	6.3 in [16.0 cm]
Package Height	0.8 in [2.0 cm]
Shipping (Package) Weight	6.2 oz [175.0 g]

---

**What's in the Box**

Included in Package	1 - Mini DisplayPort to VGA Adapter Cable
---------------------	---

---

*\*Product appearance and specifications are subject to change without notice.*