

15 ft Mini DisplayPort to VGA Adapter Converter Cable – mDP to VGA 1920x1200 - White

Product ID: MDP2VGAMM15W



The MDP2VGAMM15W active Mini DisplayPort to VGA converter cable lets you connect your Mini DisplayPort-equipped desktop or laptop directly to a VGA monitor or projector at a longer distance than a standard-length cable would support, while saving the expense of additional adapters. The cable features a stylish white design, that is well-suited for connecting Mac computers. It is also the perfect accessory for any of your Microsoft Surface Pro devices with mDP.

Plus, because the converter cable supports video resolutions up to 1920x1200 you can convert a DisplayPort video source to VGA without sacrificing video quality.

The MDP2VGAMM15W is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Connect your existing VGA display device (monitor, projector) to a DisplayPort output device (PC, laptop, Mac, Ultrabook)
- Use your VGA monitor as a secondary display, connected to a Mini DisplayPort output
- Connect a Mini DisplayPort computer to a VGA projector for presentations or meetings in a boardroom or auditorium setting

Features

- Active Mini DisplayPort to VGA conversion

- Supports resolutions up to 1920x1200 (WUXGA) and HDTV resolutions up to 1080p
- Compatible with Intel Thunderbolt devices that are capable of outputting a DisplayPort signal
- Plug-and-Play Installation

Hardware

| | |
|---------------------------|------------------------|
| Warranty | 3 Years |
| Active or Passive Adapter | Active |
| AV Input | Mini DisplayPort - 1.2 |
| AV Output | VGA |
| Audio | No |
| Chipset ID | Analogix - 9832 |

Performance

| | |
|-----------------------------|----------------------------|
| Maximum Cable Length | 15.0 ft [4.6 m] |
| Maximum Analog Resolutions | 1920x1200 / 1080p (Output) |
| Maximum Digital Resolutions | 1920x1200 / 1080p (Input) |
| Audio Specifications | VGA - No Audio Support |

Connector(s)

| | |
|-------------|----------------------------------|
| Connector A | Mini-DisplayPort (20 pin) |
| Connector B | VGA (15 pin, High Density D-Sub) |

Environmental

| | |
|-----------------------|---------------------------|
| Operating Temperature | 0C to 60C (32F to 140F) |
| Storage Temperature | -10C to 70C (14F to 158F) |
| Humidity | 40%-85%RH |

Physical Characteristics

| | |
|--------------|-----------------|
| Color | White |
| Cable Length | 15.0 ft [4.6 m] |



| | |
|-------------------|-----------------|
| Product Length | 15.0 ft [4.6 m] |
| Product Width | 1.3 in [34 mm] |
| Product Height | 0.6 in [15 mm] |
| Weight of Product | 8.3 oz [234 g] |

Packaging Information

| | |
|---------------------------|------------------|
| Package Length | 8.9 in [22.5 cm] |
| Package Width | 7.8 in [19.7 cm] |
| Package Height | 0.6 in [15 mm] |
| Shipping (Package) Weight | 8.6 oz [243 g] |

What's in the Box

| | |
|---------------------|---------------------------------------|
| Included in Package | Mini DisplayPort to VGA Adapter Cable |
|---------------------|---------------------------------------|

****Product appearance and specifications are subject to change without notice.***

