

3ft (91cm) Mini DisplayPort to VGA Adapter Converter Cable – mDP to VGA 1920x1200 - White

**Product ID:** MDP2VGAMM3W



The MDP2VGAMM3W active Mini DisplayPort to VGA converter cable lets you connect your Mini DisplayPort-equipped desktop or laptop directly to a nearby VGA monitor or projector, saving the expense of additional adapters while eliminating the clutter of excess cable. The converter features a stylish white design, that is well-suited for connecting Mac computers. It is also the perfect accessory for any of your Microsoft Surface Pro devices with mDP.

The adapter cable is compatible with Intel Thunderbolt, when connected directly to a supporting DisplayPort over Thunderbolt I/O port. Plus, because the converter cable supports video resolutions up to 1920x1200 you can convert a DisplayPort video source to VGA without sacrificing video quality.

The MDP2VGAMM3W is backed by a 3-year StarTech.com warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Use your VGA monitor as a secondary display, connected to a Mini DisplayPort output
- Connect a Mini DisplayPort computer to a VGA projector for presentations or meetings in a boardroom or auditorium setting
- Connect your existing VGA display device (monitor, projector) to a DisplayPort output device (PC, laptop, Mac, Ultrabook)

## Features

- Active Mini DisplayPort to VGA conversion
- Plug-and-Play Installation
- Supports resolutions up to 1920x1200 (WUXGA) and HDTV resolutions up to 1080p
- Compatible with Intel Thunderbolt devices that are capable of outputting a DisplayPort signal

---

### Hardware

Warranty	3 Years
Active or Passive Adapter	Active
AV Input	Mini DisplayPort - 1.2
AV Output	VGA
Audio	No
USB Pass-Through	No
Chipset ID	Analogix - 9832

---

### Performance

Maximum Cable Length	3.0 ft [0.9 m]
Maximum Analog Resolutions	1920x1200 / 1080p (Output)
Maximum Digital Resolutions	1920x1200 / 1080p (Input)
Audio Specifications	VGA - No Audio Support

---

### Connector(s)

Connector A	1 - Mini-DisplayPort (20 pin)
Connector B	1 - VGA (15 pin, High Density D-Sub)

---

### Environmental

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	40%-85%RH

---

**Physical  
Characteristics**

Color	White
Cable Length	3.0 ft [0.9 m]
Product Length	36.6 in [93 cm]
Product Width	1.3 in [3.4 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	2.8 oz [78 g]

---

**Packaging  
Information**

Package Quantity	1
Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.7 in [18 mm]
Shipping (Package) Weight	0.2 lb [0.1 kg]

---

**What's in the Box**

Included in Package	Mini DisplayPort to VGA Adapter Cable
---------------------	---------------------------------------

---

***\*Product appearance and specifications are subject to change without notice.***