

6 ft Mini DisplayPort to VGA Adapter Converter Cable – mDP to VGA 1920x1200 - Black

Product ID: MDP2VGAMM6B

The MDP2VGAMM6B 6ft active Mini DisplayPort to VGA converter cable lets you connect your Mini DisplayPort-equipped device (such as a Macbook or any Microsoft Surface Pro devices with mDP) directly to a VGA monitor or projector with no additional adapters or cables required -- a cost-effective solution for enabling your Mini DisplayPort computer to work with a VGA monitor or projector.

The adapter cable is compatible with Intel Thunderbolt, when connected directly to a supporting DisplayPort over Thunderbolt I/O port. Plus, because the converter cable supports video resolutions up to 1920x1200 you can convert a DisplayPort video source to VGA without sacrificing video quality.

The MDP2VGAMM6B is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Use your VGA monitor as a secondary display, connected to a Mini DisplayPort output
- Connect a Mini DisplayPort computer to a VGA projector for presentations or meetings in a boardroom or auditorium setting
- Connect your existing VGA display device (monitor, projector) to a DisplayPort output device (PC, laptop, Mac, Ultrabook)

Features

- Active Mini DisplayPort to VGA conversion
- Plug-and-Play Installation
- Supports resolutions up to 1920x1200 (WUXGA) and HDTV resolutions up to 1080p
- Compatible with Intel Thunderbolt devices that are capable of outputting a DisplayPort signal

Hardware

Warranty	3 Years
Active or Passive Adapter	Active
AV Input	Mini DisplayPort - 1.2
AV Output	VGA
Audio	No

Chipset ID Analogix - 9832

Performance

Maximum Cable Length	6.0 ft [1.8 m]
Maximum Analog Resolutions	1920x1200 / 1080p (Output)
Maximum Digital Resolutions	1920x1200 / 1080p (Input)
Audio Specifications	VGA - No Audio Support
MTBF	1,449,804 hours

Connector(s)

Connector A	Mini-DisplayPort (20 pin)
Connector B	VGA (15 pin, High Density D-Sub)

Environmental

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	40%-85%RH

Physical Characteristics

Color	Black
Cable Length	6.0 ft [1.8 m]
Product Length	6.0 ft [1.8 m]
Product Width	1.5 in [37.0 mm]
Product Height	0.7 in [19.0 mm]
Weight of Product	3.6 oz [101.3 g]

Packaging Information

Package Length	8.7 in [22.2 cm]
Package Width	7.8 in [19.7 cm]
Package Height	0.8 in [20.0 mm]



Shipping (Package) Weight	4.3 oz [123.0 g]
------------------------------	------------------

**What's in the
Box**

Included in Package	Mini DisplayPort to VGA Adapter Cable
---------------------	---------------------------------------

****Product appearance and specifications are subject to change without notice.***

