

6 ft Mini DisplayPort to VGA Adapter Converter Cable – mDP to VGA 1920x1200 - White

Product ID: MDP2VGAMM6W



The MDP2VGAMM6W 6ft active Mini DisplayPort to VGA converter cable lets you connect your Mini DisplayPort-equipped device (such as a Macbook or any Microsoft Surface Pro devices with mDP) directly to a VGA monitor or projector with no additional adapters or cables required -- a cost-effective solution for enabling your Mini DisplayPort computer to work with a VGA monitor or projector. The cable features a stylish white design, that is well-suited for connecting Mac computers.

The adapter cable is compatible with Intel Thunderbolt, when connected directly to a supporting DisplayPort over Thunderbolt I/O port. Plus, because the converter cable supports video resolutions up to 1920x1200 you can convert a DisplayPort video source to VGA without sacrificing video quality.

The MDP2VGAMM6W is backed by a 3-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Use your VGA monitor as a secondary display, connected to a Mini DisplayPort output
- Connect a Mini DisplayPort computer to a VGA projector for presentations or meetings in a boardroom or auditorium setting
- Connect your existing VGA display device (monitor, projector) to a DisplayPort output device (PC, laptop, Mac, Ultrabook)

Features

- Active Mini DisplayPort to VGA conversion

- Plug-and-Play Installation
- Supports resolutions up to 1920x1200 (WUXGA) and HDTV resolutions up to 1080p
- Compatible with Intel Thunderbolt devices that are capable of outputting a DisplayPort signal

Hardware	Warranty	3 Years
	Active or Passive Adapter	Active
	AV Input	Mini DisplayPort - 1.2
	AV Output	VGA
	Audio	No
	Chipset ID	Analogix - 9832
Performance	Maximum Cable Length	6.0 ft [1.8 m]
	Maximum Analog Resolutions	1920x1200 / 1080p (Output) 1920x1200 / 1080p (Input)
	Maximum Digital Resolutions	VGA - No Audio Support
	Audio Specifications	
Connector(s)	Connector A	Mini-DisplayPort (20 pin)
	Connector B	VGA (15 pin, High Density D-Sub)
Environmental	Operating Temperature	0C to 60C (32F to 140F)
	Storage Temperature	-10C to 70C (14F to 158F)
	Humidity	40%-85%RH
Physical Characteristics	Color	White
	Cable Length	6.0 ft [1.8 m]
	Product Length	36.0 in [9.2 cm]
	Product Width	1.6 in [40 mm]
	Product Height	0.6 in [15 mm]
	Weight of Product	3.3 oz [94.6 g]
Packaging Information	Package Length	8.8 in [2.2 cm]
	Package Width	7.8 in [2.0 cm]
	Package Height	0.6 in [15 mm]
	Shipping (Package) Weight	4.2 oz [120 g]

What's in the Box	Included in Package	Mini DisplayPort to VGA Adapter Cable
--------------------------	---------------------	---------------------------------------

**Product appearance and specifications are subject to change without notice.*

