

3ft (91cm) Mini DisplayPort Extension Cable - 4K x 2K Video - Mini DisplayPort Male to Female Extension Cord - mDP 1.2 Extender Cable - Works with Mini DP or Thunderbolt 2 Mac/PC

Product ID: MDPEXT3



This Mini DisplayPort 1.2 cable lets you extend the connection distance between your Mini DP devices by up to 3 feet.

The cable delivers the ideal solution for better placement of peripheral devices and can be used to connect your Microsoft Surface Pro 4, Surface Book, MacBook, MacBook Pro, MacBook Air, and other mDP enabled devices to Apple's LED Cinema Display or other Mini DisplayPort monitor.

Simply connect your tablet or laptop to the extension cable using a standard Mini DisplayPort Cable and connect the extension cable to your Mini DP monitor.

The cable supports high resolutions of up to 4k x 2k (3840 x 2160) @ 60Hz with a maximum HBR2 bandwidth of 21.6 Gbps. The cable also supports Multi-Stream (MST) for daisy chaining multiple monitors and provides optional audio support.

The MDPEXT3 is backed by StarTech.com's lifetime warranty, for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

Please note: Newer laptop and desktop computers (e.g. Apple) come equipped with Thunderbolt ports only. Our Mini DisplayPort Cables can be connected to the Thunderbolt ports, enabling you to connect your Mini DP compatible displays.

Certifications, Reports and Compatibility



Applications

- Extend the connection distance between your Microsoft Surface Pro 4, Surface Book, MacBook, MacBook Pro, MacBook Air, Mac Pro, iMac, or Mac Mini and Apple LED Cinema Display monitor, by 3 feet

Features

- **MINI DISPLAYPORT 1.2 CABLE:** This 91cm Mini DisplayPort v1.2 cable supports 4K x 2K video (3840x2400p 60Hz), 21.6 Gbps bandwidth, HBR2, 8Ch Audio, Multi-Stream Transport (MST), GTC for precise audio channel timing & 3D Stereo (2560x1600p 120Hz)
- **COMPATIBILITY NOTE:** This is not a Thunderbolt cable and is not compatible with Thunderbolt peripherals such as Docking Stations, Displays or External Enclosures; It can however be used to connect a Thunderbolt 2 laptop to a Mini-DisplayPort monitor
- **RELIABLE DESIGN:** Durable ABS connectors with flexible PVC strain relief and jacket prevents fraying or damage due to bending or rough usage; Metal connector sub-structure provides EMI shielding
- **QUALITY CONSTRUCTION:** 30AWG wire with gold-plated connectors for improved signal integrity & reliability; Superior EMI shielding with double sided copper foil provides higher quality video and audio; mDP cable is Backward compatible with DP1.1
- **SPECS:** 3 feet (91 cm); Black Mini DP Cable; DisplayPort v1.2; mDP Male to mDP Female Cord; 30 AWG; PVC cable jacket, ABS connector shell; Shield: Al-Mylar foil with Braid; Protocols: HBR2, MST, GTC; Backed for Life

Hardware

Warranty	Lifetime
Number of Conductors	20
Connector Plating	Gold
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG

Connector(s)

Connector A	1 - Mini-DisplayPort (20 pin)
Connector B	1 - Mini-DisplayPort (20 pin)

Physical Characteristics

Color	Black
Connector Style	Latching

Wire Gauge	32 AWG
Cable Length	3.0 ft [0.9 m]
Product Length	36.0 in [91.4 cm]
Product Width	0.5 in [1.2 cm]
Product Height	0.4 in [0.9 cm]
Weight of Product	1.2 oz [33.0 g]

Packaging Information

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.4 in [1.0 cm]
Shipping (Package) Weight	1.5 oz [42.0 g]

What's in the Box

Included in Package	1 - 3 ft Mini DisplayPort 1.2 Video Extension Cable - M/F
---------------------	---

****Product appearance and specifications are subject to change without notice.***