

3ft (1m) Mini DisplayPort Cable - 4K x 2K Ultra HD Video - Mini DisplayPort 1.2 Cable - Mini DP to Mini DP Cable for Monitor - mDP Cord works w/ Thunderbolt 2 Ports - White

Produkt ID: MDPMM1MW



The MDPMM1MW 1m White Mini DisplayPort™ 1.2 cable features 2 Mini DP male connectors, and offers a dependable solution for connecting any Mini DisplayPort-enabled laptop (including Mac® family of products) to a Mini DisplayPort-equipped monitor.

The mDP cable supports high resolutions of up to 4k x 2k (3840 x 2160) @ 60Hz with a maximum HBR2 bandwidth of 21.6 Gbps. The cable also supports Multi-Stream (MST) for daisy chaining multiple monitors and provides optional audio support.

The MDPMM1MW is backed by StarTech.com's Lifetime Warranty, for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

Please note: Newer laptop and desktop computers (e.g. Apple®) come equipped with Thunderbolt™ ports only. Our Mini DisplayPort Cables can be connected to the Thunderbolt ports, enabling you to connect your Mini DP compatible displays.

## Certifikat, rapporter och kompatibilitet

### Användning

- Connecting your Mini DisplayPort products to a Mini DisplayPort compatible display

### Funktioner

- MINI DISPLAYPORT 1.2 CABLE: This 3.3 ft (1m) Mini DisplayPort v1.2 cable supports 4K x 2K

(3840x2400p 60Hz), 21.6 Gbps bandwidth , HBR2, 8Ch Audio, Multi-Stream Transport (MST), GTC for precise audio channel timing & 3D Stereo (2560x1600p 120Hz)

- **RELIABLE DESIGN:** Durable ABS connectors with flexible PVC strain relief and jacket prevents fraying or damage due to bending or rough usage; Metal connector sub-structure provides EMI shielding; Mini DisplayPort cable works with Thunderbolt 2 ports
- **QUALITY CONSTRUCTION:** 30AWG wire with gold-plated connectors for improved signal integrity & reliability; Superior EMI shielding with double sided copper foil provides higher quality video and audio; mDP cable is backwards compatible with DP 1.1
- **APPLICATIONS:** Ideal for home/office/boardroom/classroom works w/laptop (with TB2/Mini-DP port)/professional workstations with FirePro™ W9100/8100, NVS 810/510 graphic card; UHD/4K monitor/projector/display; Apple MacBook Pro/Air, Microsoft Surface Pro 1-6
- **SPECS:** 3.3 feet (1 meter) | White Mini DisplayPort Cable | DisplayPort v1.2 | Mini-DP Male to Mini-DP Male Cord | 30 AWG | PVC cable jacket, ABS connector shell | Shield: Al-Mylar foil with Braid | Protocols: HBR 2, MST, GTC | Lifetime Warranty

---

#### Hårdvara

Garantipolicy	Lifetime
Antal ledare	19
Kontaktplätering	Guld
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Aluminiummylarfolie med jord-tråd
Brandteknisk klass	CMG-klass (General Purpose)

---

#### Prestanda

Maximal digital upplösning	4k x 2k (3840 x 2160) @ 60Hz
----------------------------	------------------------------

---

#### Kontakt(er)

Connector A	Mini-DisplayPort (20-stifts)
Connector B	Mini-DisplayPort (20-stifts)

---

#### Utseende

Färg	Vit
Tråddimension	32 AWG

Kabellängd	39.4 in [100 cm]
Produktlängd	39.4 in [100.0 cm]
Produktbredd	0.4 in [10.0 mm]
Produkt höjd	0.3 in [8.0 mm]
Produktvikt	1.5 oz [43.0 g]

---

#### Förpackning

Förpackningsantal	1
Package Length	7.9 in [20.0 cm]
Package Width	8.7 in [22.0 cm]
Package Height	0.4 in [10.0 mm]
Fraktvikt (förpackning)	1.5 oz [43.0 g]

---

#### Vad det är i lådan

Ingår i paketet	1 m White Mini DisplayPort 1.2 Cable - M/M
-----------------	--

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

