

Aluminum Travel A/V Adapter: 3-in-1 Mini DisplayPort to VGA, DVI or HDMI - 4K

Product ID: MDPVGDVHD4K



This 3-in-1 travel adapter offers a portable solution for connecting your Mini DisplayPort computer to a VGA, DVI or HDMI display.

The adapter is VESA certified, to ensure compatibility with your mDP computer.

This travel adapter has been constructed with a sturdy aluminum housing and features a pure white Mini DisplayPort cable built in. While the adapter looks great and works well with any mDP device, it's designed to seamlessly match your MacBook Air or MacBook Pro.

Instead of filling your laptop bag with different converters for different displays, this 3-in-1 adapter gives you all the video outputs you'll need. With VGA, DVI and HDMI outputs, this adapter lets you connect from your laptop's Mini DisplayPort port to any boardroom or classroom display, without the inconvenience of carrying a separate adapter for each display type.

With support for multiple video outputs and a lightweight, small-footprint design, this adapter is the ideal plug-and-play solution for travel or BYOD (Bring Your Own Device) applications around the office.

The adapter features a built-in magnetic fastener, for cable management. The magnet helps guide the breakout cable into place for quick and secure storage while traveling, ensuring the adapter is neatly stored in your travel bag.

The HDMI output on this adapter supports Ultra HD 4K resolutions, providing four times the picture quality of high-definition 1080p. The HDMI output is also backward compatible with lower resolutions, such as 1080p and 720p, so the adapter is also perfect for your legacy video equipment. The VGA and DVI outputs also support a high-definition maximum resolution up to 1920 x 1200, so you can still enjoy excellent video quality.

The travel adapter is compatible with mDP Intel Thunderbolt devices that are capable of outputting a DisplayPort signal.

The MDPVGDVHD4K is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Keep the adapter with you while traveling, to connect to virtually any display you come across
- Connect your BYOD MacBook Pro or MacBook Air to a provided VGA, DVI, or HDMI display at work
- Connect a VGA, DVI, or HDMI display to your Mini DisplayPort laptop, to use as a secondary monitor

Features

- 3-in-1 adapter - mDP to VGA, mDP to DVI and mDP to HDMI
- Maximum portability with built-in magnetic cable manager
- Astonishing picture quality with support for UHD 4K
- Compatible with mDP Intel Thunderbolt devices that are capable of outputting a DisplayPort signal
- VESA certified
- Plug-and-play installation
- Small footprint
- Lightweight design

Hardware

Warranty	3 Years
AV Input	Mini DisplayPort - 1.2
AV Output	HDMI - 1.4
	VGA
	DVI-I (Digital Only) - Single-Link
Audio	Yes

Performance

Maximum Cable Distance	49.9 ft [15.2 m]
------------------------	------------------

To Display	
Video Revision	DisplayPort 1.2
Maximum Analog Resolutions	1920 x 1200
Maximum Digital Resolutions	3840 x 2160
Supported Resolutions	HDMI output: 3840 x 2160, 2560 x 1600, 1920 x 1200, 1920 x 1080, 1280 x 720
	DVI and VGA output: 1920 x 1200, 1920 x 1080, 1280 x 720
Wide Screen Supported	Yes
Audio Specifications	HDMI - 7.1 Channel Audio
	DVI - No Audio Support
	VGA - No Audio Support
General Specifications	Only one video output is supported on the video adapter at a time. If multiple connections are made, only one of the outputs will function.
MTBF	1,133,293 hours

Connector(s)

Connector A	1 - Mini-DisplayPort (20 pin)
Connector B	1 - HDMI (19 pin)
	1 - VGA (15 pin, High Density D-Sub)
	1 - DVI-D (25 pin)

Special Notes / Requirements

Note	<p>The HDMI port is a passive port.</p> <p>The DVI-D is a passive port.</p> <p>The VGA port is an active port.</p> <p>Maximum Cable Distance to Display refers to digital video. VGA distance capabilities are dependent upon the quality of your cabling</p>
------	---

Environmental

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	40%-50%RH

Physical Characteristics

Color	Silver
Accent Color	White
Cable Length	4.3 in [110 mm]
Product Length	4.1 in [10.3 cm]
Product Width	2.2 in [5.5 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	4.3 oz [121.0 g]

Packaging Information

Package Quantity	1
Package Length	5.8 in [14.7 cm]
Package Width	6.8 in [17.3 cm]
Package Height	1.3 in [3.2 cm]
Shipping (Package) Weight	6.3 oz [179.0 g]

What's in the Box

Included in Package	1 - travel A/V adapter
---------------------	------------------------

****Product appearance and specifications are subject to change without notice.***