

3m VGA Monitorkabel - Hochauflösendes Koaxial HD15 Videokabel - St/Bu

Produkt-ID: MXT101HQ10



This 10ft High Resolution VGA Extension Cable is designed to provide the highest video quality possible through VGA.

Ideally suited for high resolution VGA applications, this high quality male to female coaxial VGA extension cable helps to eliminate picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection by using ferrite cores near the connector ends.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Extends your VGA monitor cable

Merkmale

- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief

- Ideal for high resolution monitors (1920x1200 and above)
- Ferritkern eliminiert EMI-Interferenzen

Hardware

Garantiebestimmungen Lifetime

Steckverbinderplatten Nickel

Steckverbinder

Steckverbinder A 1 - VGA (15-polig, High Density D-Sub)

Steckverbinder B 1 - VGA (15-polig, High Density D-Sub)

Spezielle Hinweise/Anforderungen

Hinweis Pin number 9 is not populated on these connectors

Physische Eigenschaften

Farbe	Schwarz
Kabellänge	10.0 ft [3.0 m]
Produktlänge	10.0 ft [3.0 m]
Produktbreite	1.3 in [3.4 cm]
Produkthöhe	0.6 in [1.5 cm]
Produktgewicht	12.9 oz [366.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	13.5 in [34.4 cm]
Paketbreite	5.3 in [13.5 cm]
Pakethöhe	1.7 in [4.3 cm]
Versandgewicht (Verpackung)	13.3 oz [376.0 g]

Verpackungsinhalt

Im Paket enthalten	10 FOOT COAXIAL CABLE
--------------------	-----------------------

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.