

10 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F

ID prodotto: MXT101HQ10



This 10ft High Resolution VGA Extension Cable is designed to provide the highest video quality possible through VGA.

Ideally suited for high resolution VGA applications, this high quality male to female coaxial VGA extension cable helps to eliminate picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection by using ferrite cores near the connector ends.

Certificazioni, report e compatibilità

Applicazioni

- Extends your VGA monitor cable

Caratteristiche

- Ideal for high resolution monitors (1920x1200 and above)
- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Nuclei in ferrite per eliminare le interferenze elettromagnetiche
- Molded connector ends with strain relief

Hardware

Norme di garanzia Lifetime

Placcatura connettori Nichel

Connettore/i

Connettore A VGA (15 pin, D-Sub ad alta densità)

Connettore B VGA (15 pin, D-Sub ad alta densità)

Note/requisiti speciali

Nota Pin number 9 is not populated on these connectors

Caratteristiche fisiche

Colore Nero

Lunghezza cavo 10.0 ft [3.0 m]

Lunghezza prodotto 10.0 ft [3.0 m]

Larghezza prodotto 1.3 in [33.8 mm]

Altezza prodotto 0.6 in [15.1 mm]

Peso prodotto 12.9 oz [366 g]

Informazioni confezione

Package Length 12.9 in [32.7 cm]

Package Width 4.6 in [11.7 cm]

Package Height 0.9 in [22 mm]

Peso spedizione (confezione) 13.3 oz [378 g]

Contenuto della confezione

Incluso nella confezione 10 FOOT COAXIAL CABLE



* L'aspetto e le specifiche dell'articolo sono soggetti a modifiche senza preavviso.

