

10 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F

Productcode: MXT101HQ10



This 10ft High Resolution VGA Extension Cable is designed to provide the highest video quality possible through VGA.

Ideally suited for high resolution VGA applications, this high quality male to female coaxial VGA extension cable helps to eliminate picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection by using ferrite cores near the connector ends.

Certificaties, rapporten en compatibiliteit



Toepassingen

- Extends your VGA monitor cable

Eigenschappen

- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief

- Ideal for high resolution monitors (1920x1200 and above)
- Ferrietkern elimineert EMI-interferentie

Hardware

Garantiebeleid	Lifetime
Connectormateriaal	Nikkel

Connector(en)

Connector A	1 - VGA (15-polig, D-Sub met hoge dichtheid)
Connector B	1 - VGA (15-polig, D-Sub met hoge dichtheid)

Speciale opmerkingen / vereisten

Notitie	Pin number 9 is not populated on these connectors
---------	---

Fysieke eigenschappen

Kleur	Zwart
Kabellengte	10.0 ft [3.0 m]
Lengte product	10.0 ft [3.0 m]
Breedte product	1.3 in [3.4 cm]
Hoogte product	0.6 in [1.5 cm]
Gewicht product	12.9 oz [366.0 g]

Verpakkingsinformatie

Verpakkingsaantal	1
Lengte Verpakking	13.5 in [34.4 cm]
Package Width	5.3 in [13.5 cm]
Package Height	1.7 in [4.3 cm]
Verzendgewicht (verpakt)	13.3 oz [376.0 g]

Wat wordt er
meegeleverd

Meegeleverd

10 FOOT COAXIAL CABLE

Garantiebepalinge
n

Warranty

Levenslang

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.