

## 10 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F

**Product ID:** MXT101HQ10



This 10ft High Resolution VGA Extension Cable is designed to provide the highest video quality possible through VGA.

Ideally suited for high resolution VGA applications, this high quality male to female coaxial VGA extension cable helps to eliminate picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection by using ferrite cores near the connector ends.

### **Certifications, Reports and Compatibility**

### **Applications**

- Extends your VGA monitor cable

### **Features**

- Ideal for high resolution monitors (1920x1200 and above)
  - Triple-coaxial + twisted-pair wire for crystal clear display
  - Impedance matched at 75 Ohms for full brightness and vibrant picture color
  - Ferrite core eliminates EMI interference
  - Molded connector ends with strain relief
-

## Hardware

Warranty	Lifetime
Connector Plating	Nickel

---

## Connector(s)

Connector A	VGA (15 pin, High Density D-Sub)
Connector B	VGA (15 pin, High Density D-Sub)

---

## Special Notes / Requirements

Note	Pin number 9 is not populated on these connectors
------	---

---

## Physical Characteristics

Color	Black
Cable Length	10.0 ft [3.0 m]
Product Length	10.0 ft [3.0 m]
Product Width	1.3 in [33.8 mm]
Product Height	0.6 in [15.1 mm]
Weight of Product	12.9 oz [366 g]

---

## Packaging Information

Package Length	12.9 in [32.7 cm]
Package Width	4.6 in [11.7 cm]
Package Height	0.9 in [22 mm]
Shipping (Package) Weight	13.3 oz [378 g]

---

## What's in the Box

Included in Package	10 FOOT COAXIAL CABLE
---------------------	-----------------------

---

***\*Product appearance and specifications are subject to change without notice.***

