

35 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F

Productcode: MXT101HQ35



This 35ft High Resolution VGA Extension Cable is designed to provide the highest video quality possible through VGA.

Ideally suited for high resolution VGA applications, this high quality male to female coaxial VGA extension cable helps to eliminate picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection by using ferrite cores near the connector ends.

Certificaties, rapporten en compatibiliteit



Toepassingen

Eigenschappen

- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Ferrite core eliminates EMI interference
- Molded connector ends with strain relief

- Ideal for high resolution monitors (1920x1200 and above)

Hardware

Garantiebeleid	Lifetime
Connectormateriaal	Nikkel
Type kabelmantel	PVC - Polyvinyl Chloride

Connector(en)

Connector A	1 - VGA (15-polig, D-Sub met hoge dichtheid)
Connector B	1 - VGA (15-polig, D-Sub met hoge dichtheid)

Speciale opmerkingen / vereisten

Notitie	Pin number 9 is not populated on these connectors
---------	---

Fysieke eigenschappen

Kleur	Grijs
Draaddikte	28 AWG
Kabellengte	35.0 ft [10.7 m]
Lengte product	35.0 ft [10.7 m]
Breedte product	0.0 in [0.0 cm]
Hoogte product	0.0 in [0.0 cm]
Gewicht product	2.3 lb [1.1 kg]

Verpakkingsinformatie

Verpakkingsaantal	1
Lengte Verpakking	8.4 in [21.3 cm]
Package Width	8.7 in [22.1 cm]
Package Height	2.7 in [6.9 cm]

Verzendgewicht (verpakt)	2.4 lb [1.1 kg]
-----------------------------	-----------------

Wat wordt er
meegeleverd

Meegeleverd	35 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F
-------------	--

Garantiebepalinge
n

Warranty	Levenslang
----------	------------

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.