

3 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F

Product ID: MXT101HQ3



This 3ft High Resolution VGA Extension Cable is designed to provide the highest video quality possible through VGA.

Ideally suited for high resolution VGA applications, this high quality male to female coaxial VGA extension cable helps to eliminate picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection by using ferrite cores near the connector ends.

Certifications, Reports and Compatibility

Applications

- Extends your VGA monitor cable

Features

- Ideal for high resolution monitors (1920x1200 and above)
- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Ferrite core eliminates EMI
- Molded connector ends with strain relief

Connector(s)

Warranty	Lifetime
Connector A	VGA (15 pin, High Density D-Sub)
Connector B	VGA (15 pin, High Density D-Sub)

Special Notes / Requirements

Note	Pin number 9 is not populated on these connectors
------	---

Physical Characteristics

Color	Black
Cable Length	36.0 in [91.4 cm]
Product Length	36.0 in [91.4 cm]
Weight of Product	6.7 oz [190 g]

Packaging Information

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.9 in [22 mm]
Shipping (Package) Weight	7.0 oz [199 g]

What's in the Box

Included in Package	3 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F
---------------------	--

**Product appearance and specifications are subject to change without notice.*

