

150 ft Coax High Resolution Monitor VGA Extension Cable - HD15 M/F

Product ID: MXT101HQ_150



This 150ft High Resolution VGA Extension Cable is designed to provide the highest video quality possible through VGA.

Ideally suited for high resolution VGA applications, this high quality male to female coaxial VGA extension cable helps to eliminate picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection by using ferrite cores near the connector ends.

Certifications, Reports and Compatibility

Applications

- Extends your VGA monitor cable

Features

- Ideal for high resolution monitors (1920x1200 and above)
 - Triple-coaxial + twisted-pair wire for crystal clear display
 - Impedance matched at 75 Ohms for full brightness and vibrant picture color
 - Ferrite core eliminates EMI interference
 - Molded connector ends with strain relief
-

Connector(s)

Warranty	Lifetime
Connector A	VGA (15 pin, High Density D-Sub)
Connector B	VGA (15 pin, High Density D-Sub)

Special Notes / Requirements

Note	Pin number 9 is not populated on these connectors
------	---

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	150.0 ft [45.7 m]
Product Length	150.0 ft [45.7 m]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	9.0 lb [4.1 kg]

Packaging Information

Package Length	13.8 in [35.0 cm]
Package Width	2.8 in [72.0 mm]
Package Height	17.7 in [45.0 cm]
Shipping (Package) Weight	9.0 lb [4.1 kg]

What's in the Box

Included in Package	150 FOOT COAXIAL CABLE
	Nuts

**Product appearance and specifications are subject to change without notice.*

