

25 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F

Product ID: MXT101HQ_25



This 25ft High Resolution VGA Extension Cable is designed to provide the highest video quality possible through VGA.

Ideally suited for high resolution VGA applications, this high quality male to female coaxial VGA extension cable helps to eliminate picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection by using ferrite cores near the connector ends.

Certifications, Reports and Compatibility

Applications

- Extends your VGA monitor cable

Features

- Ideal for high resolution monitors (1920x1200 and above)
 - Triple-coaxial + twisted-pair wire for crystal clear display
 - Impedance matched at 75 Ohms for full brightness and vibrant picture color
 - Ferrite core eliminates EMI interference
 - Molded connector ends with strain relief
-

Hardware

| | |
|-------------------|----------|
| Warranty | Lifetime |
| Connector Plating | Nickel |

Connector(s)

| | |
|-------------|----------------------------------|
| Connector A | VGA (15 pin, High Density D-Sub) |
| Connector B | VGA (15 pin, High Density D-Sub) |

Special Notes / Requirements

| | |
|------|---|
| Note | Pin number 9 is not populated on these connectors |
|------|---|

Physical Characteristics

| | |
|-------------------|-----------------|
| Color | Black |
| Wire Gauge | 28 AWG |
| Cable Length | 25.0 ft [7.6 m] |
| Product Length | 25.0 ft [7.6 m] |
| Weight of Product | 27.6 oz [782 g] |

Packaging Information

| | |
|---------------------------|------------------|
| Package Length | 6.8 in [17.2 cm] |
| Package Width | 7.1 in [18 cm] |
| Package Height | 2.5 in [64 mm] |
| Shipping (Package) Weight | 28.3 oz [802 g] |

What's in the Box

| | |
|---------------------|-----------------------|
| Included in Package | 25 FOOT COAXIAL CABLE |
| | Nuts |

****Product appearance and specifications are subject to change without notice.***

