

6 ft Coax High Res Low Profile VGA Monitor Extension Cable - HD15 M/F

Product ID: MXT101LP6



StarTech.com's High Resolution Monitor VGA Extension Cables are designed to provide the highest video quality available through a VGA connection.

These superthin lightweight cables come with slim low profile HDDB15 connectors, and are perfect for carrying in your laptop bag, or to minimize cable clutter in desktop environments. They eliminate the annoying "ghosting" and fuzzy images inherent with non-coaxial cables.

Certifications, Reports and Compatibility



Applications

- Extends VGA/SVGA monitor cable
- Lightweight video cable for laptop

Features

- Ideal for high resolution monitors (1024x768 and above)
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief

Connector(s)

| | |
|-------------|--------------------------------------|
| Warranty | Lifetime |
| Connector A | 1 - VGA (15 pin, High Density D-Sub) |
| Connector B | 1 - VGA (15 pin, High Density D-Sub) |

Physical Characteristics

| | |
|--------------|----------------|
| Color | Black |
| Cable Length | 6.0 ft [1.8 m] |

Packaging Information

| | |
|---------------------------|------------------|
| Package Quantity | 1 |
| Package Length | 4.9 in [12.4 cm] |
| Package Width | 0.6 in [15 mm] |
| Package Height | 8.7 in [22 cm] |
| Shipping (Package) Weight | 0.3 lb [0.1 kg] |

Warranty Information

| | |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

****Product appearance and specifications are subject to change without notice.***