

10 ft VGA Monitor Cable - HD15 MM

Product ID: MXT101MM10



This 10-foot VGA Video Monitor Cable features two HD15 (male) connectors, providing a reliable VGA connection.

For best performance, this VGA extension cable is designed to be used with low-resolution applications. For applications that require higher resolutions, see our 10ft Coax VGA Cable (MXT101MMHQ10).

MXT101MM10 is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connects a PC's VGA port to a switchbox
- Connect a VGA display to a VGA source

Features

- Supports low resolution applications
 - Guaranteed reliability
-

Hardware

Warranty	Lifetime
Connector Plating	Nickel

Connector(s)

Connector A	VGA (15 pin, High Density D-Sub)
Connector B	VGA (15 pin, High Density D-Sub)

Special Notes / Requirements

Note	Pin number 9 is not populated on these connectors
------	---

Physical Characteristics

Color	Gray
Cable Length	10.0 ft [3.0 m]
Product Length	10.0 ft [3.0 m]
Product Width	1.3 in [3.3 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	6.0 oz [170.0 g]

Packaging Information

Package Quantity	1
Package Length	7.9 in [20.0 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.0 in [0.1 mm]
Shipping (Package) Weight	6.2 oz [175.0 g]

What's in the Box

Included in Package	1 - 10 ft VGA Monitor Cable - HD15 MM
---------------------	---------------------------------------

****Product appearance and specifications are subject to change without notice.***