

10 ft VGA Monitor Cable - HD15 MM

Product ID: MXT101MM10



This 10-foot VGA Video Monitor Cable features two HDDB15 (male) connectors, providing a reliable VGA connection.

For best performance, this VGA extension cable is designed to be used with low-resolution applications. For applications that require higher resolutions, see our [%product id="MXT101MMHQ10" text="10ft Coax VGA Cable"%] (MXT101MMHQ10).

MXT101MM10 is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connects a PC's VGA port to a switchbox
- Connect a VGA display to a VGA source

Features

- Supports low resolution applications
- Guaranteed reliability

Hardware	Warranty	Lifetime
	Connector Plating	Nickel

Connector(s)	Connector A	VGA (15 pin, High Density D-Sub)
	Connector B	VGA (15 pin, High Density D-Sub)

Special Notes / Requirements	Note	Pin number 9 is not populated on these connectors
-------------------------------------	------	---------------------------------------------------

Physical Characteristics	Color	Gray
	Cable Length	10.0 ft [3.0 m]
	Product Length	10.0 ft [3.0 m]
	Product Width	1.3 in [33 mm]
	Product Height	0.6 in [15 mm]
	Weight of Product	6.0 oz [170.000 g]

Packaging Information	Package Length	7.9 in [2.0 cm]
	Package Width	4.9 in [1.2 cm]
	Package Height	0.0 in [0.070 mm]
	Shipping (Package) Weight	6.2 oz [175.000 g]

What's in the Box	Included in Package	10 ft VGA Monitor Cable - HD15 MM
--------------------------	---------------------	-----------------------------------

**Product appearance and specifications are subject to change without notice.*

