

## 6 ft Monitor VGA Cable - HD15 M/M

Product ID: MXT101MM



This 6-foot VGA Video Monitor Cable features two HDDB15 (male) connectors, providing a reliable VGA connection.

For best performance, this VGA extension cable is designed to be used with low-resolution applications. For applications that require higher resolutions, see our [%product id="MXT101MMHQ" text="6ft Coax VGA Cable"%] (MXT101MMHQ).

MXT101MM is backed by a StarTech.com lifetime warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Connects a PC's VGA port to a switchbox
- Connect a VGA display to a VGA source

### Features

- Supports low resolution applications
- Guaranteed reliability

---

<b>Hardware</b>	Warranty	Lifetime
	Connector Plating	Nickel
	Cable Jacket Material	PVC - Polyvinyl Chloride

	Cable Shield Material	Aluminum-Mylar Foil with Braid
<b>Connector(s)</b>	Connector A	VGA (15 pin, High Density D-Sub)
	Connector B	VGA (15 pin, High Density D-Sub)
<b>Special Notes / Requirements</b>	Note	Pin number 9 is not populated on these connectors
<b>Physical Characteristics</b>	Color	Gray
	Wire Gauge	28 AWG
	Cable Length	6.0 ft [1.8 m]
	Product Length	6.0 ft [1.8 m]
	Product Width	1.3 in [33 mm]
	Product Height	0.7 in [18 mm]
	Weight of Product	4.3 oz [122 g]
<b>Packaging Information</b>	Package Length	8.9 in [2.2 cm]
	Package Width	4.9 in [1.2 cm]
	Package Height	0.5 in [13 mm]
	Shipping (Package) Weight	4.5 oz [127 g]
<b>What's in the Box</b>	Included in Package	6 ft VGA Monitor Cable - HD15 M/M

***\*Product appearance and specifications are subject to change without notice.***

