

Cable VGA coaxial haute resolution HD15 - M/M

N° de produit: MXT101MMHQ3



The MXT101MMHQ3 3-foot High Resolution VGA Monitor Cable is designed to provide the highest video quality possible through VGA and is ideally suited for high resolution VGA applications of 1920x1200 and above.

This durably constructed coaxial VGA cable features two HD15 (male) connectors and eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial cables, while providing superior EMI interference protection by using ferrite cores near the connector ends.

## Certifications, rapports et compatibilité

### Applications

- Ideal for high resolution monitors (1920x1200 and above)
- Connect any VGA display to a VGA source
- Connect a high resolution display to a Desktop PC or video switch, up to 3 feet away

### Spécifications techniques

- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief

- Ferrite core eliminates EMI interference

---

#### Matériel

Politique de garantie	Lifetime
Nombre de conducteurs	14
Placage du connecteur	Nickel
Type de gaine de câble	PVC - Polyvinyl Chloride
Type de blindage du câble	Feuille d'aluminium-Mylar avec blindage tressé
Résistance au feu	Homologué CMG (usage général)
Nombre de tores magnétiques	1
Approbations réglementaires	UL2919

---

#### Performance

Impédance	75 Ohm
-----------	--------

---

#### Connecteur(s)

Connecteur A	VGA (15 broches , D-Sub haute densité)
Connecteur B	VGA (15 broches , D-Sub haute densité)

---

#### Conditions environnementales

Température de fonctionnement	0 to 60 °C
Température de stockage	-20 to 80 °C
Humidité	0 - 80 %RH

---

#### Caractéristiques physiques

Couleur	Noir
---------	------



Calibre du fil	28 AWG
Dimensions max. du connecteur	1.3 in [34 mm]
Longueur de câble	36.0 in [91.4 cm]
Dia. ext. du câble	0.4 in [9 mm]
Longueur du produit	36.0 in [91.4 cm]
Largeur du produit	1.3 in [32 mm]
Hauteur du produit	0.6 in [15 mm]
Poids du produit	6.4 oz [180 g]

---

Informations d'emballage

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.7 in [17 mm]
Poids brut	6.7 oz [189 g]

---

Contenu du paquet

Inclus dans le paquet	3 ft Coax High Resolution VGA Monitor Cable - HD15 M/M
	Nuts

---

\* L'apparence et les spécifications du produit peuvent être modifiées sans préavis

