

3 ft Coax High Resolution Monitor VGA Cable - HD15 M/M

Produkt ID: MXT101MMHQ3



The MXT101MMHQ3 3-foot High Resolution VGA Monitor Cable is designed to provide the highest video quality possible through VGA and is ideally suited for high resolution VGA applications of 1920x1200 and above.

This durably constructed coaxial VGA cable features two HD15 (male) connectors and eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial cables, while providing superior EMI interference protection by using ferrite cores near the connector ends.

Certifikat, rapporter och kompatibilitet

Användning

- Ideal for high resolution monitors (1920x1200 and above)
- Connect any VGA display to a VGA source
- Connect a high resolution display to a Desktop PC or video switch, up to 3 feet away

Funktioner

- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedence matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief

- Ferrite core eliminates EMI interference

Hårdvara

Garantipolicy	Lifetime
Antal ledare	14
Kontaktplätering	Nickel
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Aluminiummylarfolie med flätning
Brandteknisk klass	CMG-klass (General Purpose)
Antal ferriter	1
Rättsliga godkännanden	UL2919

Prestanda

Impedans	75 Ohm
----------	--------

Kontakt(er)

Connector A	VGA (15-stifts, High Density D-Sub)
Connector B	VGA (15-stifts, High Density D-Sub)

Miljö

Drifttemperatur	0 to 60 °C
Förvaringstemperatur	-20 to 80 °C
Luftfuktighet	0 - 80 %RH

Utseende

Färg	Svart
Tråddimension	28 AWG
Maximal kontaktdimension	1.3 in [34 mm]
Kabellängd	36.0 in [91.4 cm]



Yttre kabelldiameter	0.4 in [9 mm]
Produktlängd	36.0 in [91.4 cm]
Produktbredd	1.3 in [32 mm]
Produkt höjd	0.6 in [15 mm]
Produktvikt	6.4 oz [180 g]

Förpackning

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.7 in [17 mm]
Fraktvikt (förpackning)	6.7 oz [189 g]

Vad det är i lådan

Ingår i paketet	3 ft Coax High Resolution VGA Monitor Cable - HD15 M/M
	Nuts

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

