

3 ft Coax High Resolution Monitor VGA Cable - HD15 M/M

Product ID: MXT101MMHQ3



The MXT101MMHQ3 3-foot High Resolution VGA Monitor Cable is designed to provide the highest video quality possible through VGA and is ideally suited for high resolution VGA applications of 1920x1200 and above.

This durably constructed coaxial VGA cable features two HD15 (male) connectors and eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial cables, while providing superior EMI interference protection by using ferrite cores near the connector ends.

Certifications, Reports and Compatibility

Applications

- Ideal for high resolution monitors (1920x1200 and above)
- Connect a high resolution display to a Desktop PC or video switch, up to 3 feet away
- Connect any VGA display to a VGA source

Features

- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Ferrite core eliminates EMI interference
- Molded connector ends with strain relief

Hardware

Warranty	Lifetime
Number of Conductors	14
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Number of Ferrites	1
Regulatory Approvals	UL2919

Performance

Impedance	75 Ohm
-----------	--------

Connector(s)

Connector A	VGA (15 pin, High Density D-Sub)
Connector B	VGA (15 pin, High Density D-Sub)

Environmental

Operating Temperature	0 to 60 C
Storage Temperature	-20 to 80 C
Humidity	0 - 80 %RH

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Max Connector Dimension	1.3 in [34 mm]
Cable Length	36.0 in [91.4 cm]
Cable OD	0.4 in [9 mm]
Product Length	36.0 in [91.4 cm]



Product Width	1.3 in [32 mm]
Product Height	0.6 in [15 mm]
Weight of Product	6.4 oz [180 g]

Packaging Information

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	0.7 in [17 mm]
Shipping (Package) Weight	6.7 oz [189 g]

What's in the Box

Included in Package	3 ft Coax High Resolution VGA Monitor Cable - HD15 M/M
	Nuts

****Product appearance and specifications are subject to change without notice.***

