

## 45 ft Coax High Resolution Monitor VGA Cable - HD15 M/M

Productcode: MXT101MMHQ45



The MXT101MMHQ45 High Resolution VGA Cable (45ft) is designed to provide the highest video quality possible through VGA, ideally suited for high resolution applications of 1920x1200 and above.

This durably constructed coaxial VGA video cable (HD15 to HD15) eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial VGA cables, while delivering superior EMI interference protection by using ferrite cores near the connector ends.

### Certificaties, rapporten en compatibiliteit



### Toepassingen

- Replace a worn-out or missing VGA monitor cable with this high quality, coax VGA cable
- Supports high resolution VGA monitors (1920x1200)
- Connect a high resolution display to a Desktop PC or video switch, up to 45 feet away

### Eigenschappen

- Triple-coaxial + twisted-pair wire for crystal clear display

- Durably constructed cable, with high quality HD15 connectors
- Impedance matched at 75 Ohms for full brightness and vibrant picture color from your VGA monitor
- High quality VGA connectors with molded PVC strain relief

---

#### Hardware

|                    |                                      |
|--------------------|--------------------------------------|
| Garantiebeleid     | Lifetime                             |
| Aantal geleiders   | 14                                   |
| Connectormateriaal | Nikkel                               |
| Type kabelmantel   | PVC - Polyvinyl Chloride             |
| Kabelafscherming   | Aluminium-Mylar folie met vlechtwerk |
| Brandbestendigheid | CMG goedgekeurd (algemeen doel)      |
| Aantal ferrieten   | 1                                    |

---

#### Connector(en)

|             |                                              |
|-------------|----------------------------------------------|
| Connector A | 1 - VGA (15-polig, D-Sub met hoge dichtheid) |
| Connector B | 1 - VGA (15-polig, D-Sub met hoge dichtheid) |

---

#### Gebruiksomgeving

|                     |              |
|---------------------|--------------|
| Bedrijfstemperatuur | 0 to 60 °C   |
| Opslagtemperatuur   | -20 to 80 °C |
| Vochtigheid         | 0 - 80 %RH   |

---

#### Fysieke eigenschappen

|                 |                  |
|-----------------|------------------|
| Kleur           | Zwart            |
| Draaddikte      | 28 AWG           |
| Kabellengte     | 45.0 ft [13.7 m] |
| Lengte product  | 45.0 ft [13.7 m] |
| Breedte product | 0.0 in [0.0 cm]  |
| Hoogte product  | 0.0 in [0.0 cm]  |

|                          |                          |                                                             |
|--------------------------|--------------------------|-------------------------------------------------------------|
|                          | Gewicht product          | 2.6 lb [1.2 kg]                                             |
| <hr/>                    |                          |                                                             |
| Verpakkingsinformatie    |                          |                                                             |
|                          | Verpakkingsaantal        | 1                                                           |
|                          | Lengte Verpakking        | 8.7 in [22.0 cm]                                            |
|                          | Package Width            | 8.2 in [20.8 cm]                                            |
|                          | Package Height           | 3.3 in [8.5 cm]                                             |
|                          | Verzendgewicht (verpakt) | 3.1 lb [1.4 kg]                                             |
| <hr/>                    |                          |                                                             |
| Wat wordt er meegeleverd |                          |                                                             |
|                          | Meegeleverd              | 1 - 45 ft Coax High Resolution Monitor VGA Cable - HD15 M/M |
| <hr/>                    |                          |                                                             |
| Garantiebepalingen       |                          |                                                             |
|                          | Warranty                 | Levenslang                                                  |
| <hr/>                    |                          |                                                             |

\* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.