

45 ft Coax High Resolution Monitor VGA Cable - HD15 M/M

Product ID: MXT101MMHQ45



The MXT101MMHQ45 High Resolution VGA Cable (45ft) is designed to provide the highest video quality possible through VGA, ideally suited for high resolution applications of 1920x1200 and above.

This durably constructed coaxial VGA video cable (HD15 to HD15) eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial VGA cables, while delivering superior EMI interference protection by using ferrite cores near the connector ends.

Certifications, Reports and Compatibility



Applications

- Replace a worn-out or missing VGA monitor cable with this high quality, coax VGA cable
- Supports high resolution VGA monitors (1920x1200)
- Connect a high resolution display to a Desktop PC or video switch, up to 45 feet away

Features

- Triple-coaxial + twisted-pair wire for crystal clear display
- Durably constructed cable, with high quality HD15 connectors
- Impedance matched at 75 Ohms for full brightness and vibrant picture color from your VGA monitor
- High quality VGA connectors with molded PVC strain relief

Hardware	Warranty	Lifetime
	Number of Conductors	14

Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Number of Ferrites	1

Connector(s)	Connector A	VGA (15 pin, High Density D-Sub)
	Connector B	VGA (15 pin, High Density D-Sub)

Environmental	Operating Temperature	0 to 60 C
	Storage Temperature	-20 to 80 C
	Humidity	0 - 80 %RH

Physical Characteristics	Color	Black
	Wire Gauge	28 AWG
	Cable Length	45.0 ft [13.7 m]
	Product Length	45.0 ft [13.7 m]
	Product Width	0.0 in [0 mm]
	Product Height	0.0 in [0 mm]
	Weight of Product	2.6 lb [1.2 kg]

Packaging Information	Package Quantity	1
	Package Length	13.3 in [3.4 cm]
	Package Width	10.0 in [2.6 cm]
	Package Height	2.8 in [70 mm]
	Shipping (Package) Weight	2.8 lb [1.3 kg]

What's in the Box	Included in Package	45 ft Coax High Resolution Monitor VGA Cable - HD15 M/M
--------------------------	---------------------	---

**Product appearance and specifications are subject to change without notice.*

