

55 ft Coax High Resolution Monitor VGA Cable - HD15 M/M

Productcode: MXT101MMHQ55



The MXT101MMHQ55 High Resolution VGA Cable (55ft) is designed to provide the highest video quality possible through VGA, ideally suited for high resolution applications of 1920x1200 and above.

This durably constructed coaxial VGA video cable (HD15 to HD15) eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial VGA cables, while delivering superior EMI interference protection by using ferrite cores near the connector ends.

Certificaties, rapporten en compatibiliteit



Toepassingen

- Replace a worn-out or missing VGA monitor cable with this high quality, coax VGA cable
- Supports high resolution VGA monitors (1920x1200)
- Connect a high resolution display to a Desktop PC or video switch, up to 55 feet away

Eigenschappen

- Triple-coaxial + twisted-pair wire for crystal clear display

- Durably constructed cable, with high quality HD15 connectors
- Impedance matched at 75 Ohms for full brightness and vibrant picture color from your VGA monitor
- High quality VGA connectors with molded PVC strain relief

Hardware

Garantiebeleid	Lifetime
Aantal geleiders	14
Connectormateriaal	Nikkel
Type kabelmantel	PVC - Polyvinyl Chloride
Kabelafscherming	Aluminium-Mylar folie met vlechtwerk
Brandbestendigheid	CMG goedgekeurd (algemeen doel)
Aantal ferrieten	1

Connector(en)

Connector A	1 - VGA (15-polig, D-Sub met hoge dichtheid)
Connector B	1 - VGA (15-polig, D-Sub met hoge dichtheid)

Gebruiksomgeving

Bedrijfstemperatuur	0 to 60 °C
Opslagtemperatuur	-20 to 80 °C
Vochtigheid	0 - 80 %RH

Fysieke eigenschappen

Kleur	Zwart
Draaddikte	28 AWG
Kabellengte	55.0 ft [16.8 m]
Lengte product	55.0 ft [16.8 m]
Breedte product	0.0 in [0.0 mm]
Hoogte product	0.0 in [0.0 mm]

	Gewicht product	3.5 lb [1.6 kg]
Verpakkingsinformatie		
	Verpakkingsaantal	1
	Lengte Verpakking	18.1 in [46.0 cm]
	Package Width	13.8 in [35.0 cm]
	Package Height	3.4 in [8.6 cm]
	Verzendgewicht (verpakt)	3.6 lb [1.6 kg]
Wat wordt er meegeleverd		
	Meegeleverd	1 - 55 ft Coax High Resolution Monitor VGA Cable - HD15 M/M
Garantiebepalingen		
	Warranty	Levenslang

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.