

6ft Coax High Resolution 90° Upward Angled VGA Monitor Cable - HD15 M/M

Produkt ID: MXT101MMHU6



This 6ft upward-angle VGA cable is designed to support the highest resolutions and highest video quality possible through VGA while fitting perfectly in tight connection spaces. The cable features one standard VGA connector (HD15) and one VGA connector (HD15) that is situated on an upward angle relative to the shaft of the cable, requiring only 32.4mm of space at the connection point.

Suited for high resolution VGA applications (1280x1024 and above), this high quality coaxial VGA cable eliminates picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection using ferrite cores near the connector ends.

Certifikat, rapporter och kompatibilitet

Användning

- Connecting Multimedia Servers
- POS Displays

Funktioner

- 90° Upward Angled connector with a 32.4mm depth
- Ferrite core eliminates EMI interference
- Ideal for high resolution monitors (1280x1024 and above)
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief
- Triple-coaxial + twisted-pair wire for crystal clear display

Hrdvara	Garantipolicy	Lifetime
	Kabelmanteltyp	PVC - Polyvinyl Chloride

	Antal ferriter	1
Kontakt(er)	Connector A	VGA (15-stifts, High Density D-Sub)
	Connector B	VGA (15-stifts, High Density D-Sub)
Utseende	Frg	Svart
	Trddimension	28 AWG
	Kabellngd	6.0 ft [1.8 m]
	Produktlängd	6.0 ft [1.8 m]
	Produktvikt	5.5 oz [156 g]
Frpäckning	Package Length	7.6 in [1.9 cm]
	Package Width	0.9 in [24 mm]
	Package Height	8.1 in [2.0 cm]
	Fraktvikt (frpackning)	8.5 oz [240 g]
Vad det r i ldan	Ingr i paketet	6ft Coax High Resolution Up Angle VGA Monitor Cable

** Produkters utseende och specifikationer kan komma att ndras utan frvarning.*

