

10 ft Thin Coax High Res Monitor VGA Cable -Low Profile HD15 M/M

Produkt-ID: MXT101MMLP10



The MXT101MMLP10 10-foot, Low Profile High Resolution Monitor VGA Extension Cable, is designed to provide the highest video quality available through VGA. This super-thin High Resolution Monitor VGA Cable features slim, low-profile HDDB15 connectors, and offers a lightweight design that makes a hassle-free addition to a notebook/laptop operating environment.

This premium quality High Resolution Monitor VGA Cable is backed by StarTech.com's Lifetime Warranty.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Replacement VGA/SVGA monitor cable
- Lightweight video cable for laptop
- Ideal for high resolution monitors (1024x768 and above)

Merkmale

- Impedance matched at 75 Ohms for full brightness and vibrant picture color

- Molded connector ends with strain relief

Hardware

Garantiebestimmungen	Lifetime
Steckverbinderplatten	Nickel
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Typ der Kabelabschirmung	Aluminium-Mylar-Folie mit Geflecht

Steckverbinder

Steckverbinder A	1 - VGA (15-polig, High Density D-Sub)
Steckverbinder B	1 - VGA (15-polig, High Density D-Sub)

Physische Eigenschaften

Farbe	Schwarz
Drahtstärke	32 AWG
Kabellänge	10.0 ft [3.0 m]
Produktlänge	10.0 ft [3.0 m]
Produktgewicht	5.3 oz [149 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	7.3 in [18.6 cm]
Paketbreite	5.0 in [12.7 cm]
Pakethöhe	1.1 in [2.9 cm]
Versandgewicht (Verpackung)	7.3 oz [206.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 10 ft Thin Coax High Res Monitor VGA Cable -Low
--------------------	---

Profile HD15 M/M

Garantieinformatio
nen

Warranty

Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.