

10 ft Thin Coax High Res Monitor VGA Cable -Low Profile HD15 M/M

Product ID: MXT101MMLP10



The MXT101MMLP10 10-foot, Low Profile High Resolution Monitor VGA Extension Cable, is designed to provide the highest video quality available through VGA. This super-thin High Resolution Monitor VGA Cable features slim, low-profile HDDB15 connectors, and offers a lightweight design that makes a hassle-free addition to a notebook/laptop operating environment.

This premium quality High Resolution Monitor VGA Cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Replacement VGA/SVGA monitor cable
- Lightweight video cable for laptop
- Ideal for high resolution monitors (1024x768 and above)

Features

- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief

Hardware

Warranty

Lifetime

Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Connector(s)

Connector A	VGA (15 pin, High Density D-Sub)
Connector B	VGA (15 pin, High Density D-Sub)

Physical Characteristics

Color	Black
Wire Gauge	32 AWG
Cable Length	10.0 ft [3.0 m]
Product Length	10.0 ft [3.0 m]
Weight of Product	5.3 oz [149 g]

Packaging Information

Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.8 in [20 mm]
Shipping (Package) Weight	5.4 oz [154 g]

What's in the Box

Included in Package	10 ft Thin Coax High Res Monitor VGA Cable -Low Profile HD15 M/M
---------------------	--

****Product appearance and specifications are subject to change without notice.***

