

6 ft Coax Low Profile High Resolution Monitor VGA Cable HD15 M/M

Produkt-ID: MXT101MMLP6



StarTech.com's premium VGA Cables are designed to provide the highest video quality available through VGA.

This 6ft super-thin High Resolution Monitor VGA Cable features slim, low-profile HDDB15 connectors, and offers a lightweight design that makes a hassle-free addition to a notebook/laptop operating environment.

This premium quality VGA cable is backed by StarTech.com's Lifetime Warranty.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Extends VGA/SVGA monitor cable
- Lightweight video cable for laptop

Merkmale

- Molded connector ends with strain relief

- Ideal for high resolution monitors (1024x768 and above)
- Impedance matched at 75 Ohms for full brightness and vibrant picture color

Steckverbinder

Garantiebestimmungen Lifetime

Steckverbinder A 1 - VGA (15-polig, High Density D-Sub)

Steckverbinder B 1 - VGA (15-polig, High Density D-Sub)

Umgebungsbedingungen

Betriebstemperatur -5~+70

Lagertemperatur -10~+80 best (25)

Feuchtigkeit 0~70%

Physische Eigenschaften

Farbe Schwarz

Kabellänge 6.0 ft [1.8 m]

Produktlänge 6.0 ft [1.8 m]

Produktgewicht 3.6 oz [101 g]

Verpackungsinformationen

Paketmenge 1

Paketlänge 7.2 in [18.3 cm]

Paketbreite 5.0 in [12.6 cm]

Pakethöhe 1.1 in [2.8 cm]

Versandgewicht (Verpackung) 3.7 oz [106 g]

Verpackungsinhalt

Im Paket enthalten 1 - 1 m dünnes Koaxialkabel für hochauflösende VGA-Monitore - flach HD15 M/M

Garantieinformationen

Warranty

Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.